

# GATE 1184 BRONZE

300 lb. SWP-1000 lb. WOG† • Heavy Duty Service  
Solid Wedge Disc • Rising Stem • Stainless Seat • Gland Packed  
Union Bonnet • Threaded Ends


Wear-resistant stainless seat rings are securely expanded into the body to assure trouble-free service. Normal seating wear is restricted to the bronze wedge and can be easily replaced.

## SPECIFICATIONS

1184	Conforms to: MSS SP-80, Type 2, Class 300, Threaded Ends.
------	--

## MATERIAL LIST

NO.	PART	MATERIAL	SPECIFICATION
1	Body	Bronze	ASTM B 61
2	Bonnet	Bronze	ASTM B 61
3	Wedge Disc	Bronze	ASTM B 61
4	Stem	Bronze	ASTM B 61
5	Union Bonnet Nut	Bronze	ASTM B 61
6	Seat Ring	St. Steel	ASTM A 240 TY304
7	Gland	Brass	ASTM B 124 C37700
8	Packing Nut	Brass	ASTM B 283 C37700
9	Handwheel	Mall. Iron	Commercial
10	Identification Plate	Aluminum	Commercial
11	Handwheel Nut	Brass	Commercial
12	Packing	Graphite	Commercial



## DIMENSIONS - INCHES / MILLIMETERS

UNITS	SIZE	A	B	C	C <sub>v</sub>
Inches	1/4	1.81	5.13	2.25	5.6
mm	6.4	46.1	130.2	57.2	
Inches	3/8	1.88	5.13	2.25	10.7
mm	9.5	47.6	130.2	57.2	
Inches	1/2	2.25	5.50	2.50	17.6
mm	12.7	57.2	139.7	63.5	
Inches	3/4	2.50	6.25	2.75	32.0
mm	19.1	63.5	158.8	69.9	
Inches	1	3.00	7.19	2.75	54.0
mm	25.4	76.2	182.6	69.9	
Inches	1 1/4	3.38	8.56	3.25	97.0
mm	31.8	85.8	217.5	82.6	
Inches	1 1/2	3.50	9.63	3.75	135.0
mm	38.1	88.9	244.5	95.3	
Inches	2	3.75	11.75	4.25	230.0
mm	50.8	95.3	298.5	108.0	
Inches	2 1/2	4.63	14.50	4.75	337.0
mm	63.5	117.5	368.3	120.7	
Inches	3	5.00	16.75	5.50	536.0
mm	76.2	127.0	425.5	139.7	

† Non-Shock

Rev. 5

**INNOVATION** IN EVERY VALVE



**MILWAUKEE VALVE**

www.milwaukeevalve.com

The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the Installation, Operation and Maintenance Manual (IOM) see the engineering section on our website. For the most current information access www.milwaukeevalve.com

Printed on recycled paper with soy ink. 05/05