



Bronze Ball Valve For Potable Water

Two-Piece • Standard-Port

Blow-Out Proof Stem

600 PSIG WOG

Solder Ends

UPBA150/150S* 1/2"-2"



WQA tested and Certified against WQA ORD0902 for California "lead free" compliance.

Dimensions and workmanship conform to MSS SP-110
Designed in accordance with the requirements of California AB 1953,
Vermont S 152 and Senate Bill S3874

MATERIALS LIS


ITEM	PART	MATERIALS	ASTM SPEC.
1	Body	Cast Bronze	B584 C89833
2	Tailpiece	Brass	B283 C69300
		Cast Bronze (1-1/4" & up)	B584 C89833
3	Ball	Brass w/ Hard Chrome Plating	B283 C69300
4	Seat	316 Stainless Steel (1)	A276
		RPTFE, 15% Glass Filled	
5	Stem	Brass	UNS C89833
6	Thrust Washer	316 Stainless Steel (1)	A276
		RPTFE, 25% Glass Filled	
7	Packing	PTFE	
8	Packing Nut	Brass	B16
9	Handle	Steel w/ Zinc Plating	B633
10	Hand Grip	Vinyl	
11	Handle Nut	Steel w/ Zinc Plating	B633

(1) Ball and stem are stainless for UPBA150S.

DIMENSIONS

	UNITS	3/8"	1/2"	3/4"	1"	1-1/4"	1-1/2"
		DN10	DN15	DN20	DN25	DN32	DN40
A (DIA)	INCHES	0.38	0.50	0.76	0.88	1.06	1.31
	mm	9.7	12.7	19.3	22.4	26.9	33.3
B	INCHES	2.10	2.39	3.05	3.71	4.54	5.00
	mm	51.5	58.6	74.7	90.9	111.2	122.5
C	INCHES	0.90	1.07	1.56	1.76	2.27	2.50
	mm	22.1	26.2	38.2	43.1	55.6	61.3
D	INCHES	1.80	1.89	2.13	2.29	2.67	2.85
	mm	44.1	46.3	52.2	56.1	65.4	69.8
E	INCHES	3.81	3.81	4.56	4.56	6.31	6.31
	mm	93.3	93.3	111.7	111.7	154.6	154.6
F	TUBE SIZE	.51	.63	.88	1.13	1.38	1.63
	Ø						
Cv		7	13	35	38	61	87

Note: DN (Diameter Nominal) = Metric equivalent size.



*Same design as Hammond UP8511/8513

Rev. 9

Milwaukee Valve Company
16550 W. Stratton Drive
New Berlin, WI 53151
Phone: 262-432-2700
Fax: 262-432-2701

Note: Lead free refers to the wetted surface of the pipe, fittings and fixtures in potable water systems that have a weighted average lead content 0.25%. Source: California Health and Safety Code (116875).

The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the Installation, Operation and Maintenance Manual (IOM) see the engineering section on our website. For the most current information access www.milwaukeevalve.com

