

## Wheeler Model 46453 Hydrostatic Test Pump SPECIFICATIONS

DIMENSIONS:	27" (67.5cm) L x 22" (55cm) W x 34" (85cm) H
WEIGHT:	160 lbs. 73 kg
PUMP:	Twin piston: Positive displacement type
	Inlet and Outlet Ports: ¾ " NPT
	Capacity: 10gpm, 38 ltr/Min
	Pressure: 0-400psi (27 bar)
	Operating Speed: 600rpm
	Shaft Size: 1" diameter
	Lubrication: Chasis grease
ENGINE:	6.5hp Briggs & Stratton Intek Pro, 4 cycle, gasoline
	powered, with 6-1 gear reduction
CONTROL:	Adjustable pressure relief valve
GAUGE:	Glycerin filled, 0-600psi (41 bar)
DISCHARGE HOSE:	3/4" x 10' (3m), rated 1000psi (68 bar) working
	pressure
INTAKE HOSE:	3/4" x 10' (3m) with strainer



## **FEATURES**

- ✓ Automatic and precise pressure build-up
- ✓ Isolates and maintains high pressure
- √ Adjustable automatic by-pass
- ✓ Constant volume at all pressure
- ✓ Durability
- ✓ On two wheeled cart with pneumatic tires
- ✓ Inlet strainer with stainless steel mesh filter and clear bowl