

48" Dual Fuel Range with Griddle

Model: HR 1956 DF GD / HR 1956 DF GD LP



HR 1956 DF GD / HR 1956 DF GD LP

Features:

- M Touch controls and backlit precision knobs
- ComfortLift panel
- M Pro dual stacked burner system with TrueSimmer
- M Pro infrared griddle
- ComfortClean dishwasher-safe grates
- TwinPower Convection fans
- 21 Operating modes including Self Clean
- Moisture plus
- MasterChef and MasterChef Plus automatic programs
- Wireless roast probe
- Soft Close and Soft Open
- Clean Touch Steel™ front
- Fully functional M Touch Speed Oven (Combination of Convection Oven and Microwave)
- Fully functional Warming Drawer

SPECIFICATIONS

HR 1956 DF GD — Item 25195651USA

HR 1956 DF GD LP — Item 25195652USA

Overall Unit Width	47 ¹⁵ / ₁₆ " (1217mm)
Overall Height	34 ⁹ / ₁₆ " — 36 ¹ / ₁₆ " (877.7 — 915.8mm)
Overall Unit Depth to front of control panel	26 ¹ / ₂ " (673mm)
Oven Door Clearance	22 ¹ / ₄ " (565mm)
Niche	
Minimum Cabinet Niche Width	48" (1219mm)
Minimum Cabinet Opening Height	35 ¹ / ₂ " — 37" (901.7 — 939.8mm)
Burners	
Gas Burners:	(2) 12,500 BTU; (4) 19,500 BTU
Griddle:	(1) 14,300 BTU
Total BTU Output	117,300 BTU
Gas Line Connection	1/2" NPT
Plumbing	
Water Supply Requirements	Connect to a cold water supply only. Must be connected to a shut-off valve. The water shut-off valve must be accessible after installation. The water pressure must be between 14.5 psi (1 bar) and may not exceed 145 psi (10 bar). If the pressure is higher than 145 psi (10 bar), a pressure reducing valve must be installed. The supplied hose has a length of 4'11" (1.5m). The hose must not be shortened. The entire hose length must not exceed 24'7" (7.5m).
Plumbed Hose Connection	Supplied hose: flexible braided 4'11" (1.5m) with 3/8" O.D. fitting for connection to a shut off valve
Electrical	
Electrical Requirements	120V / 240V, 60Hz, 50 Amps 120V / 208V, 60Hz, 50 Amps
Power Cord	Yes - NEMA 14-50 plug, 5' 11" (1.8m) long
Shipping	
Shipping Weight	617.3 lbs. (280kg)
Shipping Dimensions	55 ¹ / ₈ " (1400mm) W x 52" (1,294mm) H x 31 1/2" (800mm) D
Support	
Call Miele	800.843.7231
Miele Website	www.mieleusa.com
20/20 Link	2020technologies.com


48" Dual Fuel Range with Griddle

Model: HR 1956 DF GD / HR 1956 DF GD LP



PRODUCT VIEWS

Isometric




48" Dual Fuel Range with Griddle

Model: HR 1956 DF GD / HR 1956 DF GD LP



PRODUCT VIEWS

Rear View



E = Electrical connection

W = Plumbing

G = Gas connection

****PLEASE NOTE:** Anti-tip device must be fastened securely in place to all studs or floor. Please refer to the Anti-tip device section in the installation manual for further details.


48" Dual Fuel Range with Griddle

Model: HR 1956 DF GD / HR 1956 DF GD LP



PRODUCT VIEWS

Detailed Bullnose and Handel View




48" Dual Fuel Range with Griddle

Model: HR 1956 DF GD / HR 1956 DF GD LP



PRODUCT VIEWS

Cabinet View



⑥ In case of combustible construction, an additional minimum clearance of 6" (each side) is necessary.

Position	Dimension	Description	
①	13" (330 mm)	Maximum depth of top cabinet	
②	18" (457 mm)	Minimum distance to bottom edge of top cabinet	
③	35 1/2"-37" (901 - 940 mm)	Distance from floor to cooktop surface	
④	10" (254 mm)	Minimum distance to combustible surfaces	
Ⓐ	48" (1219 mm)	Width of cabinet opening	
Ⓑ	6" + Ⓐ + 6"	In case of the presence of combustible material an additional minimum clearance of 6" (each side) is necessary. Ensure local codes are observed.	
Ⓒ	37" (940 mm)	Minimum distance between the top of the cooking area and the bottom of an unprotected combustible surface.	
	36" (910 mm)	Minimum distance between the top of the cooking area and the bottom of the Miele Range Hood (DAR model with DRxB XXL Blower).	
	For all other Hoods, please consult with manufacturer's instructions for required distances.		
Ⓓ	approx. 20 1/2" (518 mm)	Maximum connection width right and left	Location of wall receptacle
Ⓔ	approx. 3 1/2" (90 mm)	Maximum connection height	
Ⓕ	approx. 2 13/16" (72 mm)	Maximum connection depth	

The hatched areas represent the installation areas for the connections.

12" (305 mm) minimum distance is necessary from back of range to combustible rear wall above countertop.