

HVAC EQUIPMENT

Source 1 Residential & Commercial Replacement Parts



Order #	Mfg. #	Description	OEM/OEM Mfg. #
S89-277 ⚠	S1-02425119000	1/4 HP Condenser Fan Motor, 850 RPM, 1-Speed, 208/230V, Single-Phase, CW, 48 Frame	A.O. Smith #F48B46A50C, GE #5KCP39JFP94, Emerson #K55HXPZZ5394
S89-278 ⚠	S1-02425121700	1/4 HP Fan Motor, 850 RPM, 1-Speed, 460V, Single-Phase, CW, 48 Frame	A.O. Smith #F48A48A50C, GE #5KCP39PGP986S, Emerson #K55HXPZZ5372
S89-280 ⚠	S1-02425820700	1/3 HP Fan Motor, 1100 RPM, 1-Speed, 208/230V, Single-Phase, CW, 48 Frame	A.O. Smith #F48L43A50, Emerson #K55HXBSA
S89-281 ⚠	S1-02425973000	3/4 HP Blower Motor, 1075 RPM, 3-Speed, 208/230V, Single-Phase, CCW, 48 Frame	A.O. Smith #F48G10A50, GE #5KCP39SGS4138S
S89-474 ⚠	S1-02425100700	1/8 HP Fan Motor, 1075 RPM, 1-Speed, 208/230V, 1-Phase, CW, 48 Frame	GE #KCP39BGP931-S, k55HXPPLY-5192, A.O. Smith F48A85A50
S89-475 ⚠	S1-02425106701	1/3 HP Blower Motor, 1075 RPM, 3-Speed, 208/230V, Single-Phase, CW, 48 Frame	GE #KCP39FGN559FS
S89-476 ⚠	S1-02425962000	1/4 HP Fan Motor, 850 RPM, 2-Speed, 208/230V, 1-Phase, CW, 48 Frame	A.O. Smith #F48L09A50, K55HDXLC-6938
S89-479 ⚠	S1-02622821000	Motor Mount - 48 Frame	York
S89-679 ⚠	S1-02426056000	1 HP Blower Motor, 1100/3, 230-1-60, CCW Eos, 48 Frame	A.O. Smith #F48G57A50
S89-699 ⚠	S1-32436086425	1 HP ECM Blower Motor, 230V	York

Replacement Motors for Commercial Equipment

⚠ **Warning:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Note: Individual product images available at www.JohnstoneSupply.com



Order #	Mfg. #	Description	OEM/OEM Mfg. #
S58-799 ⚠	S1-02538231000	Actuator Motor Damper	Honeywell #M7415A1014
S89-257 ⚠	S1-02419623716	2 HP Blower Motor, 1800 RPM, 1-Speed, 200/230/460V, 3-Phase, Rev., 56 Frame	GE #5K49TN4272X, Marathon #56T17D5502
S89-258 ⚠	S1-02419623717	3 HP Blower Motor, 1725 RPM, 1-Speed, 200/230/460V, 3-Phase, Rev., 56 Frame	GE #5K49RN4277X, Marathon #Q56T17D5515
S89-265 ⚠	S1-02424110704	3/4 HP Fan Motor, 1100 RPM, 1-Speed, 460V, Single-Phase, CW, 48 Frame	A.O. Smith #F48L23850, Emerson #K55HXKPR3444
S89-269 ⚠	S1-02424115017	1/20 HP Motor, 3400 RPM, 1-Speed, 208/230V, Single-Phase, CW, 3.3 Frame	Fasco #7121-4312
S89-272 ⚠	S1-02424115020	1/20 HP Motor, 3400 RPM, 1-Speed, 460V, Single-Phase, CW, 3.3 Frame	Fasco #7162-4563
S89-275 ⚠	S1-02431939002	1-1/4 HP Fan Motor, 1140 RPM, 1-Speed, 208/230/460, 3-Phase, Rev., 56 Frame	Magnetek #17635600, Marathon #P63-3208
S89-467 ⚠	S1-02417420700	1/2 HP Fan Motor, 1100 RPM, 1-Speed, 208/230V, Single-Phase, CCW, 48 Frame	GE #KCP37MN459GS, Magnetek #X-135658-XX
S89-470 ⚠	S1-02418397700	3/4 HP Fan Motor, 1050 RPM, 1-Speed, 460V, Single-Phase, CCW, 48 Frame	A.O. Smith #F48M16A50, Emerson #K55HXJPE-5342
S89-472 ⚠	S1-02425005004	1/10 HP Ventrator Motor, 3400 RPM, 1-Speed, 460V, 1-Phase, CW, 3.3 Frame	Fasco #7162-4548
S89-473 ⚠	S1-02425005701	1/10 HP Ventrator Motor, 3400 RPM, 1-Speed, 208/230V, 1-Phase, CW, 3.3 Frame	Fasco #7162-2984S, K33HXCAF-867
S89-703 ⚠	S1-02434550001	1/3 HP Condenser Fan Motor, 208/230V With Rainshield	A.O. Smith #F48T70A50
S89-704 ⚠	S1-02434550002	1/3 HP Fan Motor, 460-1-60 With Rainshield	A.O.S. #F48T32A50
S89-705 ⚠	S1-02434551001	3/4 HP Fan Motor, 230-1-60 With Rainshield	A.O.S. #F48T73A50
X89-686 ⚠	S1-02418395700	1/2 HP Fan Motor, 1075 RPM, 460V, CCW, 48 Frame	Marathon #48A110800, Magnetek #141867

Replacement Motors for Residential Furnaces and Air Handlers

⚠ **Warning:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Note: Individual product images available at www.JohnstoneSupply.com



Order #	Mfg. #	Description	OEM/OEM Mfg. #
S80-946 ⚠	S1-32425007000	Fan With Motor	Fasco #7062-2442
S80-948 ⚠	S1-32630614000	Fan With Motor	Fasco #7021-6691
S89-214 ⚠	S1-32425960000	Vent Fan w/ Motor & Gasket 3450 RPM, 115V, Single-Phase, 60 Hz, CCW	York
S89-477 ⚠	S1-02427519000	Ventrator Motor	Fasco #7021-10300
S89-480 ⚠	S1-02632250000	Inducer Blower Ventrator Motor	Excel Comfort #20054001
S89-481 ⚠	S1-1468-2309	1/3 HP, 1100/3, 115V, CCW, Blower Motor	York
S89-486 ⚠	S1-2845-3209	Vent Motor, 3200 RPM, 115V	Westinghouse #323P861
S89-487 ⚠	S1-3118C312P	Motor Package	Fasco #71513769
S89-502 ⚠	S1-02427653000	Vent Blower with Motor	7021-10675
S89-504 ⚠	S1-37320717002	Vent Fan Motor, 2-Stage	Fasco #7062-5765
S89-505 ⚠	S1-02425110000	1/2 HP, 115V, 1075/3, Blower Motor	A.O.S. #F48L35A50
S89-506 ⚠	S1-02435329000	Ventrator Motor	Jakel #J238-150-15304
S89-507 ⚠	S1-37320717001	Ventrator Motor with Gasket	Fasco #7062-5766
S89-676 ⚠	S1-02436031000	1/4 HP, Direct Drive Blower Motor, 1075/3, 208/230-1-60, CCW Eos, 48 Frame	A.O. Smith #F48L26A50
S89-678 ⚠	S1-02426044000	3/4 HP, Direct Drive Blower Motor, 1075/3, 208/230-1-60, CCW Eos, 48 Frame	A.O. Smith #F48L17A50
S89-707 ⚠	S1-1468-235P/A	1/2 HP, Blower Motor, 1050/3, 115-1-60, CCW Eos, 48 Frame	A.O. Smith #F48F95A48
X81-851 ⚠	S1-02435330000	Blower, Inducer, Draft	Jakel #J238-112-11262C
X89-620 ⚠	S1-02423211003	3/4 HP Blower Motor, 1060 RPM, 3-Speed, 115V, Single-Phase, CCW, 48 Frame	A.O. Smith #F48L53A50C
X89-621 ⚠	S1-02423238001	1 HP, Blower Motor, 1075/3, 115-1-60, CCW EOS, 48-Frame	A.O. Smith #F48P23A50

continued on next page