COPPER TUBING BAND HANGER

Function: Designed for the suspension of non-insulated stationary copper tubing. When proper adjustment has been

obtained, the hanger should be locked in place with an upper locknut.

Material: Carbon steel

Finish: Copper color epoxy finish

Approvals: Complies with Federal Specifications A-A-1192A (Type 7) and Manufacturers' Standardization Society

ANSI/MSS SP-58 (Type 7) which supersedes ANSI/MSS SP-69.

Ordering: Specify figure number and pipe size.

NOTE: Use of an upper locknut ensures proper performance.

Tube Size		Rod	В		Adj. C		D		Max. Rec. Load		Wt. Each	
		Size							lbs.	kN	lbs.	kg
1/2	(15)	3/8	25/16	(58.74)	19/16	(39.69)	25/8	(66.68)	610	(2.71)	.12	(.05)
3/4	(19)	3/8	21/8	(53.98)	11/4	(31.75)	29/16	(65.09)	610	(2.71)	.12	(.05)
1	(25)	3/8	2	(50.80)	1	(25.40)	29/16	(65.09)	610	(2.71)	.12	(.05)
11/4	(32)	3/8	21/16	(52.39)	15/16	(23.81)	213/16	(71.44)	610	(2.71)	.13	(.06)
11/2	(40)	3/8	25/16	(58.74)	11/16	(26.99)	31/8	(79.38)	610	(2.71)	.14	(.06)
2	(50)	3/8	25/8	(66.68)	11/8	(28.58)	311/16	(93.66)	610	(2.71)	.16	(.07)
21/2	(65)	1/2	33/16	(80.96)	11/4	(31.75)	41/2	(114.30)	610	(2.71)	.28	(.13)
3	(80)	1/2	31/2	(88.90)	15/16	(33.34)	5	(127.00)	970	(4.31)	.35	(.16)
31/2	(90)	1/2	313/16	(96.84)	13/8	(34.93)	5 ⁹ / ₁₆	(141.29)	970	(4.31)	.46	(.21)
4	(100)	1/2	4	(101.60)	15/16	(33.34)	61/16	(153.99)	1130	(5.03)	.54	(.24)

