L-3431-06MR




SERIES

L-3431-MR FIBERGLASS TWIN FRONT MRI LADDER

TYPE IAA **LBS** LOAD CAPACITY













Heavy duty aluminum gusset bracing.



Raptor Boot™ —Heavy duty boot protects fiberglass.

MODEL	LADDER SIZE	MAX. REACH	BOTTOM WIDTH	APPROX. Spread	APPROX. WEIGHT (LBS)	APPROX. Cubes
L-3431-06MR	6'	10' 5"	23"	53 1/2"	26	7.9'
L-3431-08MR	8'	12' 3"	26"	67 1/2"	34	11.4'

▶ Both sides of twin front ladders can be used simultaneously by one person plus materials. The duty rating is per side.



Non-clinical testing demonstrated that these products are MR Conditional and can be used in the MRI environment according to the following conditions:

> Static magnetic field of 3–Tesla or less

> Spatial gradient magnetic field of 720-Gauss/cm or less

IMPORTANT NOTE: This product is intended for use inside the MRI environment (in the MR system room, close to the scanner). However, this ladder is not intended to be used directly inside of the MR system itself (for example, inside of the bore of the scanner). As such, the assessment of magnetic field interactions for this relation to exposure to a 3-Tesla MR system.

FM1506



FM1500

FIBERGLASS TWIN FRONT LADDER

TYPE IA LBS. 300 LOAD CAPACITY







Inside spreader braces.





SHOX[™]—Advanced impact absorption protects fiberglass rails against damage.



Raptor Boot™ —Heavy duty boot protects fiberglass.

MODEL	LADDER SIZE	MAX. REACH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WEIGHT (LBS)	APPROX. CUBES
FM1503	3'	7' 6"	17 3/4"	31"	15	3,2'
FM1504	4'	8' 6"	18 3/4"	37 7/8"	19	4.5'
FM1505	5'	9' 5"	21"	45 1/2"	22	6.3'
FM1506	6'	10' 5"	22 1/2"	53 3/4"	26	8.2'
FM1507	7'	11' 4"	24 1/4"	60 3/4"	30	10.3'
FM1508	8'	12' 3"	25 1/4"	68 3/8"	35	12.2'
FM1510	10'	14' 2"	27 3/4"	83 7/8"	44	16.8'
FM1512	12'	16' 1"	31 3/4"	98 1/8"	62	22.9'

Both sides of twin front ladders can be used simultaneously by one person plus materials. The duty rating is per side.

FM2006



FM2000 FIBERGLASS STEPLADDER

TYPE ! LBS. 250 LOAD CAPACITY











Heavy-gauge

steel hinges.





Steel gusset bracing.



Angled aluminum slin-resistant rubber feet.

MODEL	LADDER SIZE	MAX. REACH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WEIGHT (LBS)	APPROX. CUBES
FM2004	41	8' 6"	20"	37 7/8"	17	4.7'
FM2006	61	10' 5"	23"	52 ½"	24	9'
FM2008	8'	12' 4"	25"	67 1/4"	34	11.8'
FM2010	10'	14' 3"	28"	82"	45	17.4'
FM2012	12'	16' 2"	33"	97 ½"	55	23'