

Victaulic® FireLock™ Installation-Ready™ Rigid Couplings

Style 009N and Style 109



Patented



Patented

1.0 PRODUCT DESCRIPTION

Available Sizes

- Style 009N: 1 ¼ – 12"/DN32 – DN300
- Style 109: 1 ¼ – 2 ½"/DN32 – 73.0 mm

Pipe Material

- Schedule 10, Schedule 40 or specialty carbon steel pipe listed in Section 5. For use with alternative materials and wall thicknesses please contact Victaulic.

Maximum Working Pressure

- Up to 365 psi/2517 kPa.

Function

- Joins carbon steel pipe with grooved ends conforming to [publication 25.01](#).
- Provides a rigid pipe joint designed to restrict axial or angular movement.

2.0 CERTIFICATION/LISTINGS



C104-1a/36

EN 10311
Regulation (EU)
No. 305/2011

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

System No.		Location	
Submitted By		Date	

Spec Section		Paragraph	
Approved		Date	

3.0 SPECIFICATIONS – MATERIAL

Housing: Ductile iron conforming to ASTM A 536, Grade 65-45-12. Ductile iron conforming to ASTM A 395, Grade 65-45-15, is available upon special request.

Housing Coating: (specify choice)

- Orange enamel (North America, Asia Pacific)
- Red enamel (Europe)
- Optional for Style 009N: Hot dipped galvanized

Gasket: (specify choice)

Grade “E” EPDM (Type A) Vic-Plus™ Pre-lubricated Gasket

EPDM (Violet Color Code). Applicable for wet and dry (oil-free air) fire protection systems only. Listed/Approved for continuous use in wet and dry systems. Listed/Approved for dry systems at -40°F/-40°C and above. Not compatible for use with hot water services or steam services.

NOTES

- Reference should always be made to [publication I-100](#), Victaulic Field Installation Handbook for gasket lubrication instructions.
- Services listed are General Service Guidelines only. It should be noted that there are services for which these gaskets are not compatible. Reference should always be made to [publication 05.01](#), Victaulic Gasket Selection Guide for specific gasket service guidelines and for a listing of services which are not compatible.

Bolts/Nuts: (specify choice)

Standard: Carbon steel oval neck track bolts meeting the mechanical property requirements of ASTM A449 (imperial) and ISO 898-1 Class 9.8 (M10-M16) Class 8.8 (M20 and greater). Carbon steel hex nuts meeting the mechanical property requirements of ASTM A563 Grade B (imperial) and ASTM A563M Class 9 (metric). Track bolts and hex nuts are zinc electroplated per ASTM B633 Fe/Zn 5, finish Type III (imperial) or Type II (metric).


Optional for Style 009N: Stainless steel oval neck track bolts meeting the requirements of ASTM F593, Group 2 (316 stainless steel), condition CW. Stainless steel Heavy Hex nuts meeting the requirements of ASTM F594, Group 2 (316 stainless steel), condition CW, with galling-resistant coating.¹

¹ Optional bolts/nuts are available in imperial size only.

Coupling Linkage: High Strength Steel with comparable physical properties to that of the Track Bolt (ASTM A449). Linkage is zinc electroplated per ASTM B633 Fe/Zn 5, Type III Finish.

4.0 DIMENSIONS

Style 009N Two-Bolt Installation-Ready Coupling



Size		Maximum Working Pressure ²	Maximum End Load ²	Allow. Pipe End Separation ³	Qty.	Bolt/Nut Size	Dimensions					Weight Approx. (Each)
Nominal	Actual Outside Diameter						Pre-assembled		Joint Assembled		Z	
							X	Y	X	Y		
inches DN	inches mm	psi kPa	lb N	inches mm	inches mm	inches mm	inches mm	inches mm	inches mm	inches mm	lb kg	
1 ¼ DN32	1.660 42.4	365 2517	790 3514	0.10 2.54	2	¾ × 2 M10 x 51	3.13 79	5.00 127	2.75 70	5.00 127	2.00 51	1.4 0.6
1 ½ DN40	1.900 48.3	365 2517	1035 4604	0.10 2.54	2	¾ × 2 M10 x 51	3.38 86	5.13 130	3.00 76	5.13 130	2.00 51	1.5 0.7
2 DN50	2.375 60.3	365 2517	1617 7193	0.12 3.05	2	¾ × 2 ½ M10 x 63	4.00 102	5.63 143	3.50 89	5.63 143	2.00 51	1.9 0.9
2 ½	2.875 73.0	365 2517	2370 10542	0.12 3.05	2	¾ × 2 ½ M10 x 63	4.50 114	6.13 156	4.00 102	6.13 156	2.00 51	2.1 1.0
DN65	3.000 76.1	365 2517	2580 11476	0.12 3.05	2	¾ × 2 ½ M10 x 63	4.63 118	6.00 152	4.13 105	6.13 156	2.00 51	2.1 1.0
3 DN80	3.500 88.9	365 2517	3512 15622	0.12 3.05	2	¾ × 2 ½ M10 x 63	5.13 130	6.75 171	4.63 117	6.75 171	2.00 51	2.3 1.0
4 DN100	4.500 114.3	365 2517	5805 25822	0.17 4.32	2	¾ × 2 ½ M10 x 63	6.00 152	7.88 200	5.63 143	7.50 191	2.13 54	2.9 1.3
	4.250 108.0	365 2517	5178 23020	0.17 4.32	2	¾ × 2 ½ M10 x 63	5.63 152	7.38 187	5.38 137	7.38 187	2.13 54	3.1 1.4
5	5.563 141.3	365 2517	8872 39456	0.17 4.32	2	½ × 3 M12 x 76	7.25 184	9.25 235	6.75 171	9.13 232	2.25 57	5.0 2.3
	5.250 133.0	365 2517	7901 35106	0.17 4.32	2	½ × 3 M12 x 76	6.63 168	9.00 229	6.38 162	9.00 229	2.25 57	4.8 2.2
DN125	5.500 139.7	365 2517	8672 38529	0.17 4.32	2	½ × 3 M12 x 76	6.88 175	9.25 235	6.75 171	9.13 232	2.25 57	4.9 2.2
6 DN150	6.625 168.3	365 2517	12582 44469	0.17 4.32	2	½ × 3 ¼ M12 x 83	8.38 213	10.38 264	7.88 200	10.13 257	2.25 57	6.0 2.7
	6.250 159.0	365 2517	11198 49753	0.17 4.32	2	½ × 3 ¼ M12 x 83	7.88 200	10.00 254	7.38 187	9.88 251	2.25 57	5.6 2.5
	6.500 165.1	365 2517	12112 53813	0.17 4.32	2	½ × 3 ¼ M12 x 83	8.00 203	10.25 260	7.75 197	10.13 257	2.25 57	6.0 2.7
8 DN200	8.625 219.1	365 2517	21326 94863	0.17 4.32	2	¾ × 4 M16 x 101	10.88 276	13.38 340	10.25 260	13.13 333	2.50 64	11.4 5.2
	8.500 216.0	365 2517	20712 55968	0.17 4.32	2	¾ × 4 M16 x 101	10.63 270	13.25 337	10.25 260	10.13 257	2.63 67	11.4 5.2
10 DN250	10.750 273.0	300 2068	27229 121121	0.25 6.4	2	7/8 × 6 ½ M22 x 165	13.75 349	17.00 432	13.25 337	17.13 435	2.75 70	22.6 10.3
12 DN300	12.750 323.9	300 2068	38303 170380	0.25 6.4	2	7/8 × 6 ½ M22 x 165	16.00 406	19.00 483	15.50 394	19.13 486	2.75 70	27.6 12.5

² Working Pressure and End Load are total, from all internal and external loads, based on standard weight (ANSI) steel pipe, standard roll or cut grooved in accordance with Victaulic specifications. See the Listings/Approvals section of this publication for ratings on other pipe.

³ The allowable pipe separation dimension shown is for system layout purposes only. Style 009N couplings are considered rigid connections and will not accommodate expansion or contraction of the piping system.

NOTES

- When assembling Style 009N or Style 109 couplings onto end caps, take additional care to make certain the end cap is fully seated against the gasket end stop. For Style 009N or Style 109 couplings, use FireLock No. 006 end caps containing the "EZ" marking on the inside face or No. 60 end caps containing the "QV EZ" marking on the inside face. Non-Victaulic end cap products shall not be used with Style 009N or Style 109 couplings. IMPORTANT: Gaskets intended for the Style 009 or Style 009V couplings cannot be used with the Style 009N or Style 109 coupling. There is no interchanging of gaskets or housings between coupling styles.
- Use Of FlushSeal Gaskets For Dry Pipe Systems** Style 009N or Style 109 couplings are supplied with Grade "E" Type A gaskets. These gaskets include an integral pipe stop, that once installed provides the similar benefits as a FlushSeal gasket for dry pipe systems. It should be noted that standard Victaulic FlushSeal gaskets cannot be used with the Style 009N or Style 109 couplings.