tandard

# SELECTRONIC<sup>®</sup> SENSOR-OPERATED URINAL FLUSH VALVE, 1.0 GPF PWRX<sup>™</sup> 10-YEAR BATTERY SYSTEM





# **GENERAL DESCRIPTION:**

Exposed, sensor-operated Selectronic<sup>®</sup> Urinal Flush Valve for 3/4" top spud urinals. PWRX 10-Year Battery System.

## **PRODUCT FEATURES:**

- **PWRX<sup>™</sup> Battery System:** Advanced battery & electronics reduce the downtime and maintenance costs associated with changing batteries
- Safety Circuitry prevents overheating of the battery in case of short circuit, protecting the electronics
- Pressure Compensation feature ensures accurate flush volume regardless of inlet water pressure
- No Routine Maintenance: no diaphragms to replace; no filters to clean
- Self-Cleaning Piston with integral wiper spring significantly reduces clogging and maintenance
- Selectronic<sup>®</sup> Proximity System with universal sensor provides hygienic, "hands free" operation
- Dezincification Resistant brass alloy
- Fully Mechanical Manual Override Button can flush the valve without power
- Fail-Safe: Valve automatically closes upon loss of power or water pressure and does not need to be reset
- Adjustable Sanitary Flush cleans the fixture & maintains the trap seal.
- Stadium Feature: Valve automatically switches to water savings mode during periods of heavy usage
- Chemical Resistant EPDM Seals for extended life
- High Back Pressure Vacuum Breaker
- Adjustable Tailpiece
- Range can be adjusted manually or with optional remote control
- No external volume adjustment
- Can be installed left or right handed

# **RECOMMENDED SPECIFICATION:**

Electronic, sensor activated urinal flush valve shall feature self-cleaning piston valve with integral wiper spring in refill orifice to prevent clogging. Includes a long-life battery pack (with 10 year life) and fully mechanical manual override that can flush the valve without power. Includes dezincification-resistant brass valve body and metal cover with chrome finish. Includes angle stop with back-flow protection & vandal-resistant cap. Sweat solder kit and high back pressure vacuum breaker also included. 1.0 gpf/3.8 Lpf flush valve shall be American Standard Model # 6064.101.002.

#### MODEL NUMBER:

□ 6064.101.002 Exposed, sensor-operated urinal flush, 1.0 gpf.

Inlet includes 3/4" sweat solder kit and angle stop with back flow protection and vandal-resistant cap.

Outlet includes 3/4" high back pressure vacuum breaker with spud coupling and flange.

## **OPERATING PRESSURE:**

Overall Range: 20-125 psi\*\* Recommended: 20 psi (flowing) - 80 psi (static)


\*\* Water pressure over 80 psi is not recommended for most plumbing fixtures.

#### **FLOW REQUIREMENT:**

10 gpm (37.9 L/min.)

## **BATTERY LIFE:**

10 years (4,000 flushes per month)






# SELECTRONIC<sup>®</sup> SENSOR-OPERATED URINAL FLUSH VALVE, 1.0 GPF PWRX<sup>™</sup> 10-YEAR BATTERY SYSTEM

# LISTINGS:

- ASSE 1037
- ANSI/ASME A112.19.2
- ADA Compliant

# **Roughing-in Dimensions**



**Right or Left Hand Installation** 



MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES

PART OF LIXIL