UNDERGROUND CUTTING

CHAIN SAWS ACCESSORIES



PIPE CLAMP WITH MOUNTING AXLE

Reduce operator fatigue and makes safer bottom-up cuts a reality

Pipe Clamp with Mounting Axle - PN: US60410 Pipe Clamp Extension Chain - PN: US60410-3





3.5 GALLON MANUAL **PUMP WATER SUPPLY**

PART NUMBER: US27810-1



5 GALLON BATTERY POWERED PUMP


PART NUMBER: US27815



25 GALLON, 35 PSI, 12V **GATOR CLIP HOOKUP**

PART NUMBER: IC573285

HAND-HELD SAWS



HANDHELD SAWS

From plastic to ductile iron pipe, U.S.SAWS wide selection of handheld saws will get the job done. The hand-held saws are durable, direct drive tools. Because there are no extra moving parts, the hand-held saws offer the most power and durability for heavy construction cutting applications.



HAND-HELD AIR POWERED SAW

PART NUMBER: US-HS125

AIR

Hand-Held Air Saw with with Gearbox, Whip Hose, Built-In Oiler, and 14" Guard. The air saws cut from 3" to 7", depending on the model chosen. Because a pneumatic power source is used, dangerous exhaust pollutants are eliminated.

Model HS-125 Air Requirements 90 cfm @ 90 psi

RPM 3.300 **Max Cutting**

Depth

Dia. Blades Used 14" Weight 25 lbs



HAND-HELD AIR POWERED SAW

AIR

PART NUMBER: US-HS150

Hand-Held Air Saw with with Gearbox, Whip Hose, Built-In Oiler, and 18" Guard. The air saws cut from 3" to 7", depending on the model chosen. Environmentally friendly and safe alternatives to traditional gas-powered saws for cutting concrete and asphalt.

Model HS-150

Air Requirements 90 cfm @ 90 psi

RPM 3.300 Max Cutting

Depth

Dia. Blades Used 18" Weight 25 lbs