



# Miller DuraHoist™ Portable Confined Space System

## Portable & Fixed Base Options

All of the following bases are compatible with all Adjustable Mast Options. All base options include PVC liner.



### ■ Three-Piece Portable Base DH-4/

Three lightweight aluminum components for easy transport. Features adjustable aluminum screws and a built-in level indicator for easy set-up on uneven surfaces. No tools required for assembly.



### ■ Barrel Mount Sleeve w/3.5-in. (.09m) Opening DH-5/

Eight independent clamping screws allow temporary installations over edges of shoring cans, walls and other structures.



### ■ Adjustable Barrel Mount Sleeve DH-6/

Designed for shoring, wall and parapet applications where frequent set-up over varying wall thicknesses is required. Accommodates wall thicknesses up to a max. of 24-in. (.61m).



### ■ Floor Mount Sleeve DH-72P/ & DH-7SS/

Mounts to horizontal concrete or steel structures.



### ■ Wall Mount Sleeve DH-82P/ & DH-8SS/

Mounts to vertical concrete or steel structures. Compact design creates minimal intrusion into work space.



### ■ Core Mount Sleeve DH-92P/ & DH-9SS/

Designed for slip-in installation into a 4-in. (.10m) diameter core hole in concrete or in an existing steel structure.



### ■ Manhole Collar DH-11/

Designed for applications involving frequent set-ups over similarly-sized access openings. Simply slip collar into sewer manhole, tank hatch or other opening.



### ■ Flush Floor Mount Sleeve DH-202P/ & DH-20SS/

Eliminates the potential trip hazard presented by other floor mount sleeves. Installs into a 4-in. (.10m) diameter core hole in concrete or in an existing steel structure.

SKU	Description	Weight
DH-4/	Three-Piece Portable Base, Lightweight Powder-coated Aluminum	61 lbs. (27.7kg)
DH-5/	Barrel Mount Sleeve w/3.5-in. (.09m) Opening, Zinc-plated, Mild Steel	36 lbs. (16.3kg)
DH-6/	Adjustable Barrel Mount Sleeve, Anodized Welded Aluminum w/Zinc-plated Steel Hardware	56 lbs. (25.4kg)
DH-72P/	Floor Mount Sleeve, Zinc-plated, Mild Steel	13 lbs. (5.9kg)
DH-7SS/	Floor Mount Sleeve, 304 Stainless Steel	13.5 lbs. (6.1kg)
DH-82P/	Wall Mount Sleeve, Zinc-plated, Mild Steel	12 lbs. (5.4kg)
DH-8SS/	Wall Mount Sleeve, 304 Stainless Steel	13 lbs. (5.9kg)
DH-92P/	Core Mount Sleeve, Zinc-plated, Mild Steel	8 lbs. (3.6kg)
DH-9SS/	Core Mount Sleeve, 304 Stainless Steel	8 lbs. (3.6kg)
DH-11/17.5	17.5-in. (.44m) Manhole Collar for use with 18-in. to 20-in. (.46m to .51m) diameter Manways, Lightweight, Powder-coated Aluminum	26 lbs. (11.8kg)
DH-11/19.5	19.5-in. (.50m) Manhole Collar for use with 20-in. to 22-in. (.51m to .56m) diameter Manways, Lightweight, Powder-coated Aluminum	29.5 lbs. (13.4kg)
DH-11/21.5	21.5-in. (.54m) Manhole Collar for use with 22-in. to 24-in. (.56m to .61m) diameter Manways, Lightweight, Powder-coated Aluminum	33.5 lbs. (15.2kg)
DH-11/23.5	23.5-in. (.60m) Manhole Collar for use with 24-in. to 26-in. (.61m to .66m) diameter Manways, Lightweight, Powder-coated Aluminum	38 lbs. (17.2kg)
DH-11/25.5	25.5-in. (.65m) Manhole Collar for use with 26-in. to 28-in. (.66m to .71m) diameter Manways, Lightweight, Powder-coated Aluminum	43 lbs. (19.5kg)
DH-11/27.5	27.5-in. (.70m) Manhole Collar for use with 28-in. to 30-in. (.71m to .76m) diameter Manways, Lightweight, Powder-coated Aluminum	48 lbs. (21.8kg)
DH-202P/	Flush Floor Mount Sleeve, Zinc-plated, Mild Steel	24 lbs. (10.9kg)
DH-20SS/	Flush Floor Mount Sleeve, 304 Stainless Steel	25 lbs. (11.3kg)
<b>Base Accessories</b>		
DH-102P/	Sleeve Cap that keeps dirt and debris from getting into the opening of various sleeve mounts, Zinc-plated, Mild Steel	1.2 lbs. (.5kg)
DH-10SS/	Sleeve Cap that keeps dirt and debris from getting into the opening of various sleeve mounts, 304 Stainless Steel	.8 lbs. (.4kg)