# **TEST PUMPS · MANOMETER · CLOG-BUSTER**





# A) Air-Max<sup>®</sup> Pro HV Test Pump (Part #273968)

- Larger barrel diameter fewer strokes per inflation
- Contoured solid wood handle
- Forged steel construction for extra toughness
- 60 psi gauge with molded rubber cover
- Traditional metal thumb lock
- 3' hose with strain-relief
- Product Weight: 6.25 lbs (2.83 kg)



#### B) Air Max<sup>®</sup> Test Pump (Part # 273958)


- 100 psi gauge raised from base for protection
- Durable Steel Barrel
- Textured steel base prevents pump from slipping
- Durable, no-kink hose
- Product Weight: 3.6 lbs (1.36 kg)

## C) Econ-O-Pump<sup>™</sup> Test Pump (Part #273888)

- Traditional thumb lock
- 140 PSI high-pressure gauge with protective cover
- All steel construction with cast iron base
- Product Weight: 1 lb (.45 kg)

## Manometer (Part #010205)

- Used for testing gas lines and DWV pipe
- Measures water columns from 0" to 16"
- Reads in increments of 1/10"
- Product Weight: .5 lb (.23 kg)



## **CLOG-BUSTER DRAIN FLUSHER**



| PART NUMBER | PRODUCT DESCRIPTION                 |
|-------------|-------------------------------------|
| 303127      | 1" – 2" Clog-Buster drain flusher   |
| 303135      | 1.5" – 3" Clog-Buster drain flusher |
| 303143      | 4" - 6" Clog-Buster drain flusher   |
| 006193      | Faucet adapter                      |

#### **Clog-Buster Drain Flusher Features:**

- Unclogs drain pipes in seconds
- Simply remove aerator from faucet and attach faucet adapter
- Attaches to standard garden hose fitting
- Insert clog buster as far as possible into drain and slowly turn on the cold water - clog should dislodge almost immediately
- · Eliminates need for using chemicals

