# **STANLEY**



### STANLEY® POWERLOCK® TAPE RULES

- 7' blade standout (excludes 33-116 and 33-158).
- Mylar® film extends life of entire blade.
- High-impact, chrome plated ABS case.
- Secure blade lock won't creep during measurements.
- Corrosion-resistant Tru-Zero™ end hook for accurate measurements.



Product #	Blade Length (ft)	Blade Length (m)	Blade Width (in)	Stud Markings (in)	Graduation
33-116	16	-	3/4	16, 19.2	Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. First twelve inches graduated in 32nds of an inch. Remainder in 16ths of an inch. Bottom edge: Numbered in consecutive inches. First twelve inches graduated in 32nds of an inch.  Remainder in 16ths of an inch.
33-158	16	5	3/4	16, 19.2	Top edge: Major scale numbered in consecutive inches. First twelve inches graduated in 32nds of an inch. Remainder graduated in 16ths of an inch. Marked every 12 inches. Bottom edge: Major scale numbered in consecutive meters. Minor scale numbered in consecutive 10 cm repeated every 100 cm.
33-425	25	-	1	16, 19.2	Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Graduated in 16ths of an inch. Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.
33-428	26	8	1	16, 19.2	Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Graduated in 16ths of an inch. Bottom edge: Major scale numbered in consecutive meters. Minor scale numbered in consecutive 10 cm repeated every 100 cm.
33-430	30	-	1	16, 19.2	Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Graduated in 16ths of an inch. Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.
33-835	35	-	1	16, 19.2	Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Graduated in 16ths of an inch. Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.

## **STANLEY**



#### **STANLEY® VALUE PACK**

#### Product #: 90-082

- 7' blade standout.
- Mylar® film extends life of entire blade.
- High-impact, chrome plated ABS case.
- Secure blade lock won't creep during measurements.
- Corrosion-resistant Tru-Zero<sup>™</sup> end hook for accurate measurements.

Contents	Description	
1	Tape Rule (33-425)	
1	Knife (10-099)	



### **STANLEY® PREMIUM TAPE RULES**

- Rugged case design ABS structure core surrounded by rubber for superior impact resistance.
- Integrated lock protection lock button guarded by large ruber pad in case of drop.
- 10' standout best standout of MPP tapes for better efficiency.
- 1-1/8' wide blade premium feel with large easy to read numbers.



Product #	Blade Length (ft)	Blade Width (in)	Stud Markings (in)	Graduation
STHT33594S	16	1-1/8	16, 19.2	GraduationTop edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.
STHT33596LW	25	1-1/8	16, 19.2	GraduationTop edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.
STHT33597S	30	1-1/8	16, 19.2	GraduationTop edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.