## **STANLEY**

MITER BOXES

## STANLEY® CLAMPING MITER BOXES

- Made of lightweight, high impact polypropylene.
- Cam-shaped pins twist and lock with honeycomb base to secure work for accurate cuts.
- Cuts miters on 45° and 90°, face angle 45°, and all new 22-1/2° angle for octagonal shapes.
- Miter box has storage compartments to hold cam pins and pencils.
- Large design for increased cutting capacity.


Product # Type		Blade Length (in)	Points Per Inch	Teeth Per Inch
20-112	20-112 Miter Box		-	-
20-600	Miter Box with Saw	14	13	12



## STANLEY<sup>®</sup> MITER BOX WITH SAW


- Storage system holds all 12" x 14" STANLEY<sup>®</sup> back saws.
- Finger button allows easy release of saw from storage cavity.
- 90°, 45° and 22-1/2° miter slots.
- Holes in base for fastening to a workbench.
- Open interior allows cuttings to fall through.
- Integrated pencil pocket.

Product #	Blade Length (in)	Points Per Inch	Teeth Per Inch
19-800	14	14	13



## STANLEY® ADJUSTABLE ANGLE CLAMPING MITER BOX WITH SAW

- Base made of cast zinc with holes for cam-shaped pins to twist in, which secures work for accurate cuts.
- Base legs have holes for fastening to work bench.
- Base has molded in measuring marks.
- One touch angle adjustment for quick and easy angle change.
- 11 preset angle stops.
- Adjustable work stop for repetitive cuts.
- Handle is made out of high-impact polypropylene and a textured rubber grip over mold to provide comfort and a slip-resistant grip.
- Saw blade made of steel with induction-hardened teeth for long lasting sharpness.



Product #	Туре	Blade Length (in)	Blade Width (in)	Max Cutting Width at 45°	Max Cutting Width at 90°	Max Cutting Height
20-800	Miter Box with Saw	22	1-1/2	4-1/16	6-1/2	4-1/2