



INTERNAL CAST IRON PIPE CUTTER (CAPITOL STYLE CUTTER)

Cuts Cast Iron from the inside out!!

Designed to eliminate the difficulty plumbers have in setting toilet bowls, urinals and similar fixtures due to the shortness of the closet horn. Make cuts where nothing else can!

32900	3" Cast Iron.....	10 lbs. (4.5kg)
42900	4" Cast Iron.....	10.5 lbs. (4.7kg)

Replacement Cutter Wheels:

700201	Cutter Wheel for CI for 32900/42900
276097	Cutter Wheel Pin



STEEL PIPE CUTTERS

Two models designed for fast, easy cutting of steel pipes. Both models come with an extra long shank which protects adjustment threads and an extra large handle for quick, easy adjustment.

2690	For 1/8"-2" steel pipe (3.17mm-50.8mm)	6 lbs. (2.8kg)
8001	Cutter Wheel for steel	
8082	Cutter Wheel for stainless steel	
4690	For 2"-4" steel pipe (50.8mm-101.6mm)	18 lbs. (8kg)
8004	Replacement Cutter Wheel	



HINGED PIPE CUTTER

Four-wheel cutter, featuring a unique guide bar design that ensures both smooth operation and accurate precise pipe cutting. Needs only 90° to 110° handle swing, and only 4 inch clearance. Universal cutter wheels are ideal for cutting most metals and are interchangeable with many other makes of hinged pipe cutters.

5090	1/2"-2" pipe capacity (12.7mm-50.8mm)	6 lbs. (2.7kg)
95240	2"-4" pipe capacity (50.8mm-101.6mm)	18 lbs. (8.2kg)
95460	4"-6" pipe capacity (101.6mm-152.4mm)	21 lbs. (9.5kg)
95680	6"-8" pipe capacity (152.4mm-203.2mm)	27 lbs. (12kg)
95121	8"-12" pipe capacity (203.2mm-304.8mm)	35 lbs. (16kg)

Replacement Cutter Wheels:

8039	for 5090 for steel
8050	for 95041, 95240 for steel
8052	for 95061, 95460 for steel
8054	for 95081, 95680, 95121 for steel
8051	for 95041, 95240 for CI/DI
8053	for 95061, 95081, 95460, 95680, 95121 for CI/DI
8076	for 95061, 95081, 95460, 95680, 95121 / universal wheel

PIPE CLEANER (Descaler)

A versatile scraper for removing mud and scale from pipe surfaces. Makes for faster cutting and better repairs and joints. Belt material is light, strong and non-corroding. Angled blades promote self-cleaning. Belt is replaceable, longer length reduces back strain.

1300	For 3-12" diameter, 45" OAL.....	4 lbs. (2kg)
1301	Replacement Belt, 45"	3 lbs. (1.5kg)
1350	For 12-36" diameter, 72" OAL.....	5 lbs. (2.5kg)
1351	Replacement Belt, 72"	4 lbs. (2kg)

REPLACEMENT CUTTER WHEELS

WHEELER-REX		RIDGID®		REED®	
METAL TUBING CUTTERS					
CUTTER WHEEL MODEL NO.	TUBING CUTTER MODEL NO.	CUTTER WHEEL MODEL NO.	TUBING CUTTER MODEL NO.	CUTTER WHEEL MODEL NO.	TUBING CUTTER MODEL NO.
8012	9290, 9291	E1240	10, 15, 20	OSS	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8015	9290, 9291	F158	10, 15, 20	0	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8021		E2191	30, 40, 106, 108, 109, 122, 133, 134, 136, 154, 156	30-40	TC3Q, TC4Q, TC5Q, TC6Q, TC8Q
8025	9490	E2558	30, 40, 106, 108, 109, 133, 134, 136, 154, 156	30-40	TC3Q, TC4Q, TC5Q, TC6Q, TC8Q
8034		E3469	101, 103, 104, 105, 117, 118, 131, 132, 150, 151, 152, 153, 205	345T	MC2
8038	4992, 4991, 4990				
8040	2590, 3590				
8041	3790				
8044 (SS)	3790				
8045	90722	E4546	105, 131, 132, 150 - 153, 205	R4546	MC2
8046	5690, 5691, 5692			SLRCW	TC50SL, TC75SL, TC1SL
8067	90748, 90749	E2558	30, 40, 106, 108, 109, 133, 134, 136, 154, 156	30-40	TC3Q, TC4Q, TC5Q, TC6Q, TC8Q
8069	90710, 90721, 90727, 90734, 90747	F158	10, 15, 20	0	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8071	90735, 90728, 90750			73505	TC14, TC166, MC3
90799 (SS)	90724, 90730, 90764				

PLASTIC TUBING CUTTERS					
8033	4992				
8037		E2156, E5299, E2157		3-6PVC	TC3Q, TC4Q, TC5Q, TC6Q
8066	90748, 90749		30P, 40P, 133P, 134P, 136P, 154P, 156P, 106, 109P	80P	TC6Q, TC8Q
8068	90747				
8073	90750			OP2	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8074	90751				
8075	90752				

PIPE CUTTERS					
8001	2690 (Steel)	F514, M-50, F3, F3S	1, 2, 42, 300, 50, 1A, 2A, 42A, 201, 202	2RBHD	2-1, 2-1Q, 2-4WG, 2-3, 2-3Q, 2-4
8003		E1032	300, 535, 1822-1, MACH	HX2, 1/2	
8004/8016	4690 (SS) Steel	FS229S			
8006		F367	6S, 208, 209	R367	
8039	5090				
8082	2690 (SS)				
700201	32900, 42900				

HINGED CUTTERS					
8050	95041, 95240			HS4	H4
8051	95041, 95240			HS4	H4
8052	95061, 95460			HS6	H6
8053	95061, 95081, 95121, 95460, 95680			HI6	H6, H8, H12
8054	95081, 95121, 95680			HS8-12	H8, H12
8076	95061, 95081, 95121, 95460, 95680			H6PSE5	H6, H8, H12

THREADING MACHINES	
60322	WHEELER-REX MODELS 6990, 6991, 7991, 8991
60324	WHEELER-REX MODELS 7890, 6090, 7090, 8090, 6190, 6290, 6390, 6490, 6790
60390	CUTTER BLADE FOR 6794 & 6590
60310	HSS CUTTER WHEEL FOR 6790, 6793
60301	HSS CUT-OFF BLADE FOR 6794 & 6590

RIDGID IS A REGISTERED TRADEMARK OF THE RIDGE TOOL CO.
REED IS A REGISTERED TRADEMARK OF THE REED MFG. CO.