

HYDROSTATIC TEST PUMPS

MANUAL HYDROSTATIC TEST PUMPS

Ideal for testing residential water lines. Also for pressure testing small pressure tanks, sprinkler, boiler and solar systems. Lightweight and easy to use. 3/4" garden hose female inlet and 9/16"- 18 JICF male outlet. Equipped with shut off valve, gauge, and adjustable internal relief valve. 10 foot output hose included.



Features: 300psi (20 bar)

- **29200**12 lbs. (5.5kg)

Accessories:

- 3917 10' High-Pressure Output Hose
- 29250 Pump Rebuild Kit
- 34550 10' Long Suction Hose with strainer (3/4" male garden hose connection)



Features: 1000psi (68 bar)

- **29201**12 lbs. (5.5kg)

Accessories:

- 3917 10' High-Pressure Output Hose (3/8" NPT male output connection)
- 29250 Pump Rebuild Kit
- 34550 10' Long Suction Hose with strainer (3/4" male garden hose connection)



Features: 870 psi/60 bar, 1/2" connections

- **29900** with 1/2" connections.....18 lbs. (8kg)

Accessories:

- 3917 10' High-Pressure Output Hose
- 29950 Pump Repair Kit

Designed especially for use in heating, compressed air, refrigeration systems, oil installations and sprinkler systems. Complete with 2.6 gallon stainless steel integral tank and 10 ft. output hose.