

54V XR FLEXVOLT SDS PLUS 3-MODE HAMMER DRILL

DCH334X2



No Load Speed	0 - 1000rpm
Max. Drilling Capacity Concrete	30mm
Hand/Arm Vibration - drilling into Concrete	7.5m/s ²
Blows Per Minute	0 - 4480bpm
Impact Energy	3.5J



DCH334N - BARE UNIT

54V XR FLEXVOLT SDS MAX 3-MODE HAMMER DRILL

DCH481X2



No Load Speed	0 - 540rpm
Max. Drilling Capacity Concrete	40mm
Hand/Arm Vibration - drilling into Concrete	9.4m/s ²
Blows Per Minute	0 - 3150bpm
Impact Energy	6.1J



DCH481N - BARE UNIT

54V XR FLEXVOLT 48MM 8KG SDS MAX COMBINATION HAMMER

DCH733X2



Max. Drilling Capacity Concrete	48mm
Max. Drilling Capacity Core Bit	125mm
Impact Energy	13.3J
No Load Speed	177-355rpm
Blows Per Minute	1350-2705bpm
Hand/Arm Vibration - hammer drilling into Concrete	9m/s ²
Hand/Arm Vibration - chiselling	8.8m/s ²
Sound Pressure	97dB(A)
Sound Power	108dB(A)
Category	8Kg



DCH733N - BARE UNIT

54V XR FLEXVOLT ANGLE GRINDER

DCG414T2



No Load Speed	9000rpm
Hand/Arm Vibration - Grinding	5.9m/s ²
Max. Disc Diameter	125mm
Spindle Thread	M14



DCG414N - BARE UNIT

54V XR FLEXVOLT ALLIGATOR SAW

DCS397T2



Blade Length	430mm
No Load Stroke Rate	2400spm
Hand/Arm Vibration - Concrete	4.1m/s ²
Stroke Length	40mm
Blade Stop	0.2sec
Includes TCT Class 12 Blade	



Class 20 blade suitable for Poroton and Building Blocks available separately (DT2976-QZ)



DCS397N - BARE UNIT

54V XR FLEXVOLT SPLIT SHAFT STRING TRIMMER

DCM5713X1



Line Diameter	7.5m x 2.0mm
Cutting Speed	0-5100rpm/0-5500rpm
Cutting Width/Swathe	38cm
Brush Cutter	No
Sound Power Level	94dB(A)



DT20658 SPOOL & 2MM X 8.0M LINE DCM5713N BARE UNIT DT20652-QZ LINE 2.5M X 68.6M

DT20656-QZ CAP, SPOOL & LINE DT20653-QZ BRUSH CUTTER TRI BLADE

DT20654-QZ BRUSH CUTTER STRAIGHT BLADE DT20655-QZ BRUSH CUTTER 4T BLADE