RAMMERS

MIKASA RAMMERS

Features

- Four cycle engines available from Honda
- Optional shoe sizes and extensions available
- Cyclone air filtration system on MTX series
- Cam-type clutch
- Grease- and oil-bath-lubricated models



Technical specifications

MODEL	IMPACT FORCE LBS (KN)	BLOWS MIN MAX.	ENGINE MAKE MODEL	HP (KW) ¹	SHOE SIZE WIDTH IN (MM)	OPER. WEIGHT LBS (KG)
MTR40HF	1,215 (5.4)	695	HONDA GX100	2.8 (2.1)	5.9 (150)	101 (46)
MTX50HD	2,316 (10.3)	695	HONDA GX100	2.8 (2.1)	10.4 (265)	129 (59)
MTX60HD	3,064 (13.6)	695	HONDA GX100	2.8 (2.1)	10.4 (265)	141 (64)
MTX70HD	3,350 (14.9)	690	HONDA GX100	2.8 (2.1)	11.2 (285)	165 (75)
MTX70HDR	3,350 (14.9)	690	HONDA GXR120	3.5 (2.6)	11.2 (285)	165 (75)
MTX80HDR	3,505 (15.6)	678	HONDA GXR120	3.5(2.6)	11.2 (285)	181 (82)

¹ See page 50 for details.

MTX SERIES RAMMERS

4 Cycle Engines

Honda offerings to meet operator expectations of reliability and easy starts.

MTX-series rammers

feature an anti-vibration handle that significantly reduces operator fatigue.

Throttle design enables contractor to control engine speed and fuel delivery with a single lever.

Combination tachometer and engine hour meter provides engine RPM and helps track service intervals.

