

Safety Data Sheet



1. Identification

| | | | |
|-----------------------------|---|-------------------------|--|
| Product Name: | LSPR WHITE GREASE LUBRICANT | Revision Date: | 8/9/2018 |
| Product Identifier: | 273924 | Supersedes Date: | 9/15/2014 |
| Recommended Use: | Grease | | |
| Supplier: | Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA Rust-Oleum Canada (ROCA) 200 Confederation Parkway Concord, ON L4K 4T8 Canada Emergency Phone: 800-387-3625 | Manufacturer: | Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA |
| Preparer: | Regulatory Department | | |
| Emergency Telephone: | 24 Hour Hotline: 847-367-7700 | | |

2. Hazard Identification

Classification

Symbol(s) of Product



Signal Word

Danger

Possible Hazards

34% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS HAZARD STATEMENTS

| | | |
|-------------------------------------|------|--|
| Flammable Aerosol, category 1 | H222 | Extremely flammable aerosol. |
| Compressed Gas | H280 | Contains gas under pressure; may explode if heated. |
| Germ Cell Mutagenicity, category 1B | H340 | May cause genetic defects. |
| Carcinogenicity, category 1A | H350 | May cause cancer. |
| Reproductive Toxicity, category 2 | H361 | Suspected of damaging fertility or the unborn child. |

| | | |
|-------------------------------------|------|--|
| STOT, repeated exposure, category 2 | H373 | May cause damage to organs through prolonged or repeated exposure. |
| Skin Irritation, category 2 | H315 | Causes skin irritation. |

GHS LABEL PRECAUTIONARY STATEMENTS

| | |
|-----------|--|
| P210 | Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. |
| P211 | Do not spray on an open flame or other ignition source. |
| P251 | Do not pierce or burn, even after use. |
| P410+P412 | Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F. |
| P410+P403 | Protect from sunlight. Store in a well-ventilated place. |
| P201 | Obtain special instructions before use. |
| P280 | Wear protective gloves/protective clothing/eye protection/face protection. |
| P308+P313 | IF exposed or concerned: Get medical advice/attention. |
| P405 | Store locked up. |
| P501 | Dispose of contents/container in accordance with local, regional and national regulations. |
| P260 | Do not breathe dust/fume/gas/mist/vapors/spray. |
| P314 | Get medical advice/attention if you feel unwell. |
| P264 | Wash hands thoroughly after handling. |
| P302+P352 | IF ON SKIN: Wash with plenty of soap and water. |
| P321 | For specific treatment see label |
| P332+P313 | If skin irritation occurs: Get medical advice/attention. |
| P362+P364 | Take off contaminated clothing and wash it before reuse. |

3. Composition / Information On Ingredients

HAZARDOUS SUBSTANCES

| <u>Chemical Name</u> | <u>CAS-No.</u> | <u>Wt. %</u> | <u>GHS Symbols</u> | <u>GHS Statements</u> |
|-------------------------------|-----------------------|---------------------|---------------------------|------------------------------|
| Hexane | 110-54-3 | 12 | GHS02-GHS07-GHS08 | H225-304-315-336-361-373 |
| Liquefied Petroleum Gas | 68476-86-8 | 12 | GHS04-GHS08 | H280-340-350 |
| Mineral Oil | 8042-47-5 | 5.7 | Not Available | Not Available |
| Hydrotreated Light Distillate | 64742-47-8 | 3.5 | GHS08 | H304 |

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately. Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation.

FIRST AID - INGESTION: Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS LESS THAN 20°F. EXTREMELY FLAMMABLE LIQUID AND VAPOR! Water spray may be ineffective. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Closed containers may explode when exposed to extreme heat due to buildup of steam. No unusual fire or explosion hazards noted.

SPECIAL FIREFIGHTING PROCEDURES: Evacuate area and fight fire from a safe distance. Full protective equipment including self-contained breathing apparatus should be used. Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Use only in a well-ventilated area. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Avoid contact with eyes, skin and clothing.

STORAGE: Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120 ° F. Store large quantities in buildings designed and protected for storage of flammable aerosols. Contents under pressure. Do not expose to heat or store above 120 ° F. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials. Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep away from heat, sparks, flame and sources of ignition. Avoid excess heat.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

| Chemical Name | CAS-No. | Weight % Less Than | ACGIH TLV- TWA | ACGIH TLV- STEL | OSHA PEL- TWA | OSHA PEL- CEILING |
|-------------------------------|------------|-----------------------|-------------------|--------------------|------------------|----------------------|
| Hexane | 110-54-3 | 15.0 | 50 ppm | N.E. | 500 ppm | N.E. |
| Liquefied Petroleum Gas | 68476-86-8 | 15.0 | N.E. | N.E. | N.E. | N.E. |
| Mineral Oil | 8042-47-5 | 10.0 | N.E. | N.E. | N.E. | N.E. |
| Hydrotreated Light Distillate | 64742-47-8 | 5.0 | N.E. | N.E. | N.E. | N.E. |

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation. Provide general dilution of local exhaust ventilation in volume and pattern to keep TLV of hazardous ingredients below acceptable limits.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

SKIN PROTECTION: Use impervious gloves to prevent skin contact and absorption of this material through the skin. Nitrile or Neoprene gloves may afford adequate skin protection. Use gloves to prevent prolonged skin contact.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application. Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

| | | | |
|---------------------------------|---------------------|--|-----------|
| Appearance: | Aerosolized Mist | Physical State: | Liquid |
| Odor: | Solvent Like | Odor Threshold: | N.E. |
| Relative Density: | 0.484 | pH: | 9 - 11 |
| Freeze Point, °C: | N.D. | Viscosity: | N.D. |
| Solubility in Water: | None | Partition Coefficient, n-octanol/water: | N.D. |
| Decomposition Temp., °C: | N.D. | Explosive Limits, vol%: | 0.6 - 9.5 |
| Boiling Range, °C: | -18 - 427 | Flash Point, °C: | -96 |
| Flammability: | Supports Combustion | Auto-ignition Temp., °C: | N.D. |
| Evaporation Rate: | Faster than Ether | Vapor Pressure: | N.D. |
| Vapor Density: | Heavier than Air | | |

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition.

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalis.

HAZARDOUS DECOMPOSITION: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes Serious Eye Irritation

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance may cause slight skin irritation. Prolonged or repeated contact may cause skin irritation. May cause skin irritation. Allergic reactions are possible.

EFFECTS OF OVEREXPOSURE - INHALATION: Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation.

EFFECTS OF OVEREXPOSURE - INGESTION: Aspiration hazard if swallowed; can enter lungs and cause damage. Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

| <u>CAS-No.</u> | <u>Chemical Name</u> | <u>Oral LD50</u> | <u>Dermal LD50</u> | <u>Vapor LC50</u> |
|----------------|-------------------------------|------------------|--------------------|-------------------|
| 110-54-3 | Hexane | 25000 mg/kg Rat | 3000 mg/kg Rabbit | N.E. |
| 8042-47-5 | Mineral Oil | >5000 mg/kg Rat | N.E. | N.E. |
| 64742-47-8 | Hydrotreated Light Distillate | >5000 mg/kg Rat | >2000 mg/kg Rabbit | >5000 mg/L Rat |

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components. Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems. This product as supplied is a USEPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation. Do not incinerate closed containers.

14. Transport Information

| | <u>Domestic (USDOT)</u> | <u>International (IMDG)</u> | <u>Air (IATA)</u> | <u>TDG (Canada)</u> |
|-----------------------|--------------------------------------|-----------------------------|-------------------|--------------------------------------|
| UN Number: | N.A. | 1950 | 1950 | N.A. |
| Proper Shipping Name: | Paint Products in Limited Quantities | Aerosols | Aerosols | Paint Products in Limited Quantities |
| Hazard Class: | N.A. | 2.1 | 2.1 | N.A. |
| Packing Group: | N.A. | N.A. | N.A. | N.A. |
| Limited Quantity: | Yes | Yes | Yes | Yes |

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Gas under pressure, Carcinogenicity, Reproductive toxicity, Skin Corrosion or Irritation, Specific target organ toxicity (single or repeated exposure), Germ cell mutagenicity

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

16. Other Information**HMIS RATINGS**

Health: 2* Flammability: 2 Physical Hazard: 1 Personal Protection: B

NFPA RATINGS

Health: 2 Flammability: 4 Instability: 0

Volatile Organic Compounds 108 g/L

SDS REVISION DATE: 8/9/2018

REASON FOR REVISION:

Revision Description Changed
Product Composition Changed
Substance and/or Product Properties Changed in Section(s):
01 - Identification
02 - Hazard Identification
03 - Composition/Information on Ingredients
05 - Fire-fighting Measures
09 - Physical & Chemical Properties
11 - Toxicological Information
15 - Regulatory Information
16 - Other Information
Substance Hazard Threshold % Changed
Revision Statement(s) Changed

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.