Rev. 7-16 Shaded area indicates changes

## Mueller D-5 Drilling Machine - for drilling operations under pressure - 3/4" to 2" inclusive

- Catalog number D-5 (Part number 39305)
- Hand or power operation
- Designed for use on pressurized or dry mains
- Used to drill through 3/4" to 2" corporation stops and service saddles
- 14"(356 mm) boring bar travel
- Has boring bar locking mechanism
- Use on cast iron or ductile iron pipe cement lined cast iron or ductile iron pipe
  - A-C pipe PVC pipe steel pipe concrete pipe
- 500 psig (3447 kPa) maximum working pressure at 100 F (38 C)
- 250 F (121 C) maximum working temperature at 375 psig (2586 kPa)

NOTE: The working pressure or temperature rating is reduced accordingly if any attachment, valve, or fitting subjected to pressure or temperature during the drilling operation has a maximum working pressure or temperature rating less than that specified above.



## **Equipment furnished with each** D-5 machine:

- Metal storage case
- Ratchet handle (85308)
- Body gasket (33278)
- Adjustable wrench (91664)
- Two double open end wrenches (58196)
- Cutting grease (88366)
- Instruction manual (Form #9335)

## Equipment to be selected:

- Drills and drill holders page 2.9
- Shell cutters, cutter holders and pilot drills page 2.10
- Drilling machine adapter nipples page 2.11
- Power operators page 2.13



	D-5
Total shipping weight	60.5 lbs. (27 kg)
Machine only weight	35 lbs. (16 kg)
Shipping length	22-1/2"
Extended length	37"