

TUFFTRACK[™] GRASS PAVER



Tufftrack[™] Grass Pavers are the strongest paver on the market that works for both grass and gravel applications. Manufactured in rigid 24["] square panels it offers maximum strength and stabilization for support of heavy vehicles like fire trucks.

Tufftrack[™] Grass Pavers are 24" x 24" rigid panels featuring a clip fastener designed for fast installation that easily connects without extra pieces or tools. The Tufftrack Grass Paver has a combined series of 120 nested hexagonal cells per paver cell with 12 connecting clips. This unique combination provides superior stability and durability.

Ideal Applications

- Fire lanes
- Emergency vehicle access roads
- Truck maintenance and equipment yards
- Truck & cart wash-down areas
- RV & boat access and parking
- Residential driveways

- Parking lots
 - Overflow parking lots



Specifications

Tufftrack[™] is available in: 24" x 24" panels, 1.5" thick



Empty cells have a compressive strength of

86,563 psf

Cells filled with wet soil have a compressive strength of 400,000 psf

Product ships in 24 in. squares for easy layout

Unique tongue & groove clips are easier to install





Part No.	Description	Color	Pkg. Qty./ Pallet Qty.	Wt. Ea. Lbs.	Product Class
TT-24	24" x 24" Tufftrack [®] Grass Pavers	Black	1/132	4.00	55GP