


3M™ Particulate Filters and Gas/Vapor Cartridges

All 3M Particulate Filters and Gas/Vapor Cartridges can be used interchangeably with 3M™ Reusable Respirators 6000, 6500, 7000 and FF-400 Series.

3M™ Particulate Filters 2000 Series



- Lightweight and easy to breathe through
- Assortment of filters available for a wide range of applications
- Easier breathing through new 3-layer advanced Electret Filter Media in 2200 Series Filters

Part Number	Description
2071	Particulate Filter, P95
2076HF	Particulate Filter, Hydrogen Fluoride/P95, with Nuisance Level Acid Gas Relief*
2078	Particulate Filter, P95, with Nuisance Level Organic Vapor/Acid Gas Relief*
2091	Particulate Filter, P100
2096	Particulate Filter, P100, with Nuisance Level Acid Gas Relief*
2097	Particulate Filter, P100, with Nuisance Level Organic Vapor Relief*
2291	Advanced Particulate Filter, P100
2296	Advanced Particulate Filter, P100, with Nuisance Level Acid Gas Relief*
2297	Advanced Particulate Filter, P100, with Nuisance Level Organic Vapor Relief*

3M™ Particulate Filter 7093, P100

- Unique, spring-loaded filter cover design simplifies negative pressure user seal checks
- Swept-back design provides enhanced field of view and greater comfort
- 7093C offers a lightweight, low profile design that combines P100 filtration with carbon-loaded features found in heavier combination cartridge products



7093	Particulate Filter, P100
7093B	Particulate Filter, P100, Bulk
7093C	Cartridge/Filter, Hydrogen Fluoride, P100 with Nuisance Level Organic Vapor and Acid Gas Relief*

3M™ Gas/Vapor Cartridges 6000 Series



- Low-profile design helps maintain good field of vision
- Full range of cartridges to meet your needs

6001	Cartridge, Organic Vapor
6002	Cartridge, Acid Gas**
6003	Cartridge, Organic Vapor/Acid Gas**
6004	Cartridge, Ammonia/Methylamine
6005	Cartridge, Formaldehyde/Organic Vapor
6006	Cartridge, Multi Gas/Vapor**
6009	Cartridge, Mercury Vapor or Chlorine

3M™ Combination Cartridges/P100 Particulate Filters 6000 Series



- Particulate filter is permanently attached to cartridge for easy, one-step assembly
- Unique design for enhanced comfort and visibility

60921	Cartridge/Filter, Organic Vapor/P100
60922	Cartridge/Filter, Acid Gas/P100**
60923	Cartridge/Filter, Organic Vapor/Acid Gas/P100**
60924	Cartridge/Filter, Ammonia/Methylamine/P100
60925	Cartridge/Filter, Formaldehyde/Organic Vapor/P100
60926	Cartridge/Filter, Multi-Gas/Vapor/P100**
60928	Cartridge/Filter, Organic Vapor/Acid Gas/P100**†
60929	Cartridge/Filter, Mercury Vapor/Chlorine Gas/P100

* 3M recommended for relief against nuisance levels of organic vapors and acid gases. Nuisance level organic vapor and acid gas refers to concentrations not exceeding OSHA PEL or applicable government occupational exposure limits, whichever is lower. Do not use for respiratory protection against acid gases or organic vapors (except hydrogen fluoride).

** Reminder: These cartridges are approved for respiratory protection from hydrogen sulfide gas up to 10 times the permissible exposure limit (PEL) with half facepiece respirators and full facepiece respirators when qualitatively fit tested, or up to less than 300 parts per million (ppm) with full facepiece respirators when quantitatively fit tested or according to specific OSHA standards or applicable government regulations, whichever is lower. 300 ppm is the concentration considered Immediately Dangerous to Life or Health (IDLH) for hydrogen sulfide.

† As recommended by the California Department of Pesticide Regulation No. 01-009-Methyl Bromide Field Fumigation. 3M recommended for use against radioiodine and methylbromide. Note: not NIOSH approved for methylbromide or radioiodine.

For More Information

In the United States, contact:

Technical Service
1-800-243-4630

Customer Service
1-800-328-1667

Internet
www.3M.com/PPESafety

In Canada, contact:

Technical Service
1-800-267-4414

3M Canada Customer Care
1-800-364-3577

Internet
www.3M.ca/safety

For other 3M products:

Technical Service
1-800-3M-HELPS



Personal Safety Division
3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M, Scotchgard and Cool Flow are trademarks of 3M Company, used under license in Canada. Please recycle. Printed in U.S.A.
© 2013 3M Company.
All Rights Reserved.
70-0710-9082-6



WARNING

These respirators help protect against certain airborne contaminants. **Misuse may result in sickness or death.**

For proper use, the wearer must read and understand *User Instructions* provided as a part of product packaging, see supervisor, or call 3M PSD Technical Service, 1-800-243-4630. Time use limitations may apply.

Important—Before using these respirators, you must determine the following:

1. The type of contaminant(s) for which the respirator is being selected.
2. The concentration level of contaminant(s).
3. Whether the respirator can be properly fitted on the wearer's face. All respirator instructions, warnings and use and time limitations must also be read and understood by the wearer before use. Before use of these respirators, a written respiratory protection program must be implemented, meeting all the requirements of OSHA 29 CFR 1910.134, including training and fit testing.