

C16 Electric Hand Held Saw

Go Deeper - 6" Cutting Depth


Get Closer - Guard Side Removed for Flush Cutting*



1. Dust Port
2. LED Overload Light
3. Guide Rollers
4. Magnesium Blade Guard
5. Water Feed System



Removable guard side for flush cutting*



*Special flush cutting flange included.
Blade must have LYFC bolt pattern to use.

16" Blade Capacity

Electric

Features & Benefits:

- Wet or dry cutting
- Overload protection with load warning LED light - visible to operator
- Electrical cord with PRCD protection
- Detachable guide rollers
- Splash guard to protect from water spray
- Handles designed for optimal control
- Tool-free blade guard angle adjustment
- Lightweight magnesium blade guard
- Externally accessible motor brushes
- Standard water feed system with fine adjustable flow and quick release coupling and durable hose

Specifications:

Power Input:	3000 watt, 25 amp
RPM:	3900
Arbor:	1"
Max. Cutting Depth:	6"
Cut Direction:	Down
Weight:	17 lbs. (18 lbs. with guide rollers)

C16 HAND HELD ELECTRIC SAW

Model #	Motor Power	Power Source	Part #	Cat #
C16	3000 watt, 25 amp	Electric	5801605	72378

Diamond Products Limited
333 Prospect St. Elyria, OH 44035
800-321-5336 · www.diamondproducts.com

**CORE
CUT**



**DIAMOND
PRODUCTS®**