

MAX WHEELBARROWS

STRENGTH & DURABILITY

6 Cubic Foot Wheelbarrows

- All Corona® MAX Wheelbarrows feature 6 cu ft class trays, optimizing carrying capacity with typical worker's lifting ability.



Leg stabilizers help to prevent tipping by distributing the load weight



Leg stabilizers help to prevent tipping by distributing the load weight

MAX | HEAVY-DUTY CONTRACTOR WHEELBARROWS

WB 2706S | 60 IN STEEL HANDLES | 16 IN PNEUMATIC TIRE

WB 2706SFF | 60 IN STEEL HANDLES | 16 IN FLAT-FREE KNOBBY TIRE

- 1.4 mm wrinkle-free, extra-heavy-duty, powder-coated steel tray for durability
- Squared holes in tray make tightening easier, helps avoid loosening during heavy work
- Bolt-through design helps legs sustain loads better than with tabbed cross-braces
- Handles feature 10% larger cross-section than standard pro wheelbarrows
- 6 cu ft class tray balances carrying capacity with typical worker's lifting ability
- Assembly required
- Limited Lifetime Warranty

U.S. Patent D677,852

• REPLACEMENT PARTS AVAILABLE

Replacement parts fit WB 2706, WB 2706FF, WB 2706S, WB 2706SF

MAX | HEAVY-DUTY CONTRACTOR WHEELBARROWS

WB 2706 | 60 IN WOOD HANDLES | 16 IN PNEUMATIC TIRE

WB 2706FF | 60 IN WOOD HANDLES | 16 IN FLAT-FREE KNOBBY TIRE

- 1.4 mm wrinkle-free, extra-heavy-duty, powder-coated steel tray for durability
- Squared holes in tray make tightening easier, helps avoid loosening during heavy work
- Handles feature 10% larger cross-section than standard pro wheelbarrows
- Bolt-through design helps legs sustain loads better than with tabbed cross-braces
- Wheel with steel bushings and grease fitting
- Assembly required
- Limited Lifetime Warranty

U.S. Patent D677,852

• REPLACEMENT PARTS AVAILABLE

Replacement parts fit WB 2706, WB 2706FF, WB 2706S, WB 2706SF U.S. Patent D677,852



Leakproof tray



Leakproof tray

MAX | HEAVY-DUTY STEEL WHEELBARROWS

WB 2506K | 60 IN WOOD HANDLES | 16 IN PNEUMATIC TIRE

WB 2506KFF | 60 IN WOOD HANDLES | 16 IN FLAT-FREE KNOBBY TIRE

- 1.4 mm wrinkle-free, extra-heavy-duty, powder-coated steel tray for durability
- Reinforced steel front tray braces for added support and stability
- Steel wheel bushings for years of smooth performance and grease fittings for easy lubricating
- Contractor-grade hardwood handles
- Quick-connect system for faster assembly and a leak-proof tray
- With no bolts exposed on the inside of the tray, it creates a smooth finish for easier shoveling
- Assembly required
- Limited Lifetime Warranty
- **REPLACEMENT PARTS AVAILABLE**

Replacement parts fit WB 2506K, WB 2506KFF

MAX | HEAVY-DUTY STEEL WHEELBARROWS

WB 2606K | 60 IN STEEL HANDLES | 16 IN PNEUMATIC TIRE

WB 2606KFF | 60 IN STEEL HANDLES | 16 IN FLAT-FREE KNOBBY TIRE

- 1.4 mm wrinkle-free, extra-heavy-duty, powder-coated steel tray for durability
- Reinforced steel front tray braces for added support and stability
- Steel wheel bushings for years of smooth performance and grease fittings for easy lubricating
- Steel handles with comfort grips
- Quick-connect system for faster assembly and a leak-proof tray
- With no bolts exposed on the inside of the tray, it creates a smooth finish for easier shoveling
- Assembly required
- Limited Lifetime Warranty
- **REPLACEMENT PARTS AVAILABLE**

Replacement parts fit WB 2606K, WB 2606KFF