## **CONFINED SPACE & RESCUE/DESCENT**





## Miller DuraHoist™ Safety Systems

Designed for manhole and confined space entry/retrieval and fall arrest applications. The modular design allows the use of components in various configurations and applications. Multiple winches and/or lifeline systems may be mounted as required. Lightweight, manageable components for easy storage, transport and set-up.

SKU	Description
DuraHoist™ Portable (	Confined Space System
DH-1/	Four-piece system with ManHandler hoist/winch w/65-ft. of 3/16-in. galvanized steel cable
DH-2/	Four-piece system without ManHandler hoist/winch
DuraHoist™ Portable l	Fall Arrest Posts
DH-AP-1/	Portable Fall Arrest Post
DH-AP-3/	Rescue/Material Handling Davit Arm
DH-AP-9/	Portable I-beam anchor base
Miller Winch and Hois	st Mounting Brackets
8442-Z7/65FT	ManHandler® personnel-rated hoist w/65 ft. of 3/16-in. galvanized steel cable
MR50GB-Z7/50FT	MightEvac® SRL w/50 ft. of 3/16-in. galvanized wire rope, mounting bracket and carabiner
DH-19-MILLER/	Complete mounting bracket assembly required to mount a Miller ManHandler Hoist/Winch or a Miller MightEvac SRL



- Promotes quick and easy rescue with a 4:1 mechanical advantage (avg. speed of 25 ft. per minute)
- 7-ft. tripod; lightweight, high-strength aluminum construction; adjustable legs; safety chain; rubber skid pads/serrated edge tripod feet
- Corrosion-resistant stainless steel/aluminum components
- Rated for up to a 310-lb. worker
- No annual factory recertification

SKU/Length	Description
MR50GC-Z7/50FT	MightEvac w/50 ft. of 3/16-in. galvanized wire rope; 7-ft. tripod; mounting bracket, pulley, carabiner and two heavy-duty equipment bags
MR50GCM-Z7/50FT	MightEvac w/ 50-ft. of 3/16-in. galvanized wire rope; ManHandler Hoist w/ 65-ft. of 3/16-in. galvanized wire rope; 7-ft. tripod; mounting bracket, pulley, carabiner and two heavy-duty equipment bags

Models shown include connectors with 3,600-lb. gate strength



