

## SAFETY CANS





# SAFETY CANS

For nearly 60 years, our Safety Can product line has been an industry leader of galvanized Type I and Type II Safety Cans that meet OSHA and NFPA Code 30 requirements, and are UL and ULC listed and FM Approved for safe storage and handling of flammable liquids. Eagle offers FM Approved Compliance Solutions in a variety of poly and stainless cans lab cans, faucet cans, disposal cans, plunger, bench & daub cans, and poly oily waste cans to help keep your personnel and facilities protected. Made in the USA.

#### Safety Can options:

- Type I Safety Cans - Type II Safety Cans
- Type I Poly Cans
- Lab Cans

Faucet Cans DOT Cans Disposal Cans

Specialty C
Plunger Car

Bench CansDaub CansPoly Oily Waste C



Patented comfort grip trigger release plus spring closing lid with nitrile gasket that vents at 5-PSI internal pressure



Double interlock no-weld bottom seam is the only deep drawn seamless can made









18 sales@eagle-mfg.com eagle-mfg.com

### SAFETY CANS





#### **TYPE I SAFETY CANS FLAMMABLES Model Numbers** UI4S 🔥 UI10S \Lambda **UI20S** <u></u> UI25S\* <u>∧</u> **UI50S** 🔥 Model-w/Funnel UI4F Capacity 2 qt 9 in./2 Dimensions 55/16 in./ Weight 2.25 lbs Construction Galva

UI4FS 🔥	UI10FS 🛕	UI20FS 🗥	UI25FS* <u></u> ▲	UI50FS 🗘
2 qt./2 L	1 gal./3.8 L	2 gal./7.6 L	2½ gal./9.5 L	5 gal./18.9 L
9 in./22.9 cm. 5‰ in./13.5 cm.	9 in./22.9 cm. 8 in./20.4 cm.	11¼ in./28.6 cm. 9½ in./24.2 cm.	11¼ in./28.6 cm. 10 in./25.4 cm.	12½ in./31.8 cm. 13½ in./34.3 cm.
2.25 lbs./1.1 kg.	3.52 lbs./1.6 kg.	5.25 lbs./2.4 kg.	5.7 lbs./2.6 kg.	7 lbs./3.2 kg.
Galvanized	Galvanized	Galvanized	Galvanized	Galvanized
	TYPE I SAF	ETY CANS		
	D SAFET		SAFE	
UI4SY 🗘	UI10SY 🗘	UI20SY 🚣	UI25SY* ▲	UI50SY 🛕
UI4FSY 🔥	UI10FSY 🔥	UI20FSY 🔥	UI25FSY* <u>∧</u>	UI50FSY 🔥
2 qt./2 L	1 gal./3.8 L	2 gal./7.6 L	2½ gal./9.5 L	5 gal./18.9 L
9 in./22.9 cm. 5‰ in./13.5 cm.	9 in./22.9 cm. 8 in./20.4 cm.	11¼ in./28.6 cm. 9½ in./24.2 cm.	11¼ in./28.6 cm. 10 in./25.4 cm.	12½ in./31.8 cm. 13½ in./34.3 cm.
2.25 lbs./1.1 kg.	3.52 lbs./1.6 kg.	5.25 lbs./2.4 kg.	5.7 lbs./2.6 kg.	7 lbs./3.2 kg.
Galvanized	Galvanized	Galvanized	Galvanized	Galvanized

Type I Safety Cans	
<ul> <li>Eagle Type 1 Safety Cans are constructed of 24-gauge hot dipped galvanized steel, whereas other manufacturers' safety cans use</li> </ul>	* Meets the New York City Fire Code Title 29 FC 2204.4.4. Maximum 2.5 gallon (9.5 L) container regulations
lead-coated terne steel	C

 These safety cans are accepted under CARB, meet OSHA and NFPA Code 30 requirements, and are UL, ULC and FM Approved for safe handling and storage of gasoline and other flammable liquids

 Available in a variety of colors for the safe handling and storage of kerosene (blue), diesel (yellow) and combustible liquids such as oils (green)

4.1.1 Compliance: OSHA 29 CFR 1910.106, 1926.152 and NFPA Code 30

Model F15FUN Funnel











# **KEROSENE**

**Model Numbers Model-w/Funnel** Capacity **Dimensions** 

Weight

Construction

**COMBUSTIBLES** 

**Model Numbers** 

**Model-w/Funnel** 

Capacity

Weight

Capacity

Weight

**Dimensions** 

Construction

**Dimensions** 

Construction



UI4FSB 🗘

2 qt./2 L

9 in./22.9 cm.

51/4 in./13.5 cm.

2.25 lbs./1.1 kg.

Galvanized



UI10FSB 🗘

1 gal./3.8 L

9 in./22.9 cm.

8 in./20.4 cm.

3.52 lbs./1.6 kg.

Galvanized



11¼ in./28.6 cm.

9½ in./24.2 cm.

5.25 lbs./2.4 kg.

**Galvanized** 

UI20SG 🗘

UI20FSG \Lambda

2 gal./7.6 L

9½ in./24.2 cm.

Galvanized



UI50SB \Lambda UI25FSB\* ▲ UI50FSB \Lambda 2½ gal./9.5 L 5 gal./18.9 L 11¼ in./28.6 cm. 12½ in./31.8 cm. 10 in./25.4 cm. 13½ in./34.3 cm. 5.7 lbs./2.6 kg. 7 lbs./3.2 kg. Galvanized Galvanized

#### **TYPE I SAFETY CANS**

**TYPE I SAFETY CANS** 



**UI4FSG**  $\wedge$ 

2 qt./2 L

9 in./22.9 cm.

55% in./13.5 cm.

2.25 lbs./1.1 kg.

Galvanized







Galvanized





UI25SG\* ▲ UI50SG 🗘 UI25FSG\* 🔥 UI50FSG \Lambda 2½ gal./9.5 L 5 gal./18.9 L 11¼ in./28.6 cm. 12½ in./31.8 cm. 13½ in./34.3 cm. 10 in./25.4 cm. 5.7 lbs./2.6 kg. 7 lbs./3.2 kg. Galvanized Galvanized

2½ gal./9.5 L

11¼ in./28.6 cm.

9% in./24.5 cm.

8 lbs./3.7 kg.

**Stainless** 

#### **TYPE I POLY CANS**



Poly





**TYPE I STAINLESS STEEL CANS** 

14169	14545 🗥	14261	14561	14535 🗥	14540 📤	
1 gal./4 L	5 gal./19 L	2.5 gal./9.5 L	5 gal./19 L	5 gal./19 L	5 gal./19 L	
7¼ in./184 mm. 11½ in./292 mm.	11½ in./292 mm. 17 in./432 mm.	10¾ in./273 mm. 14¼ in./362 mm.	12¾ in./324 mm. 16 in./406 mm.	11½ in./292 mm. 17 in./432 mm.	11½ in./292 mm. 17 in./432 mm.	
3 lbs./1 kg.	10 lbs./4 kg.	4 lbs./2 kg.	9 lbs./4 kg.	16 lbs./7 kg.	10 lbs./4 kg.	

Poly

**Model Numbers** 14169

Poly





Poly





Poly



5 gal./19 L

11¼ in./28.6 cm.

15% in./39.7 cm.

10 lbs./4.6 kg.

**Stainless** 

DIESEL

**Model Numbers** 

Model-w/Funnel

Capacity

Weight

**Dimensions** 

Construction

Poly