

## SeeSnake® Standard Video Inspection System



A set of 35 mm pipe guides included.

### 2" to 12" (50 - 300 mm) Lines, up to 325' (99 m).

The RIDGID SeeSnake Standard video inspection system offers unmatched reliability and performance in a ruggedized package. The Standard is also available with a durable self-leveling camera head.

- 100% hardened stainless steel camera head spring assembly for optimum durability.
- Rugged, high-intensity lights for exceptional viewing and long life.
- Flexible transmitters make locating easy and are compatible with RIDGID locators.
- Can be used with any SeeSnake monitor or recorder.
- Wide pipe diameter capacity range makes this system ideal for a wide range of inspection needs.

### Specifications

- Line Capacity – 2" to 12" (50 to 300 mm).
- Maximum Run – 325' (99 m).
- Sonde – Built-in, 512 Hz.
- Reel Frame Diameter – 32" / 81 cm.
- Camera Diameter – 1.4" / 35 mm.
- Camera Length – 1.2" / 32 mm (standard).  
1" / 26 mm (Self-Leveling).
- Push Cable Diameter – .44" / 11 mm.
- Operating Temperature – 14°F – 122°F / -10°C – 50°C.
- Storage Temperature – 14° to 158°F / -10° to 70°C.
- Video Resolution – 768 × 576 px (PAL).
- Lighting – 6 LEDs (Standard) or 18 LEDs (Self-Leveling).
- Waterproof Depth – 330' (100 m) (without monitor).
- IP-Rating – IPx5 (without monitor).
- Counter – Yes.

Catalog No.	Description	Voltage (V)	Weight	
			lb.	kg
13993	SeeSnake 200' (61 m) Self-Leveling Color Reel (PAL)	230	42.0	19.0
14003	SeeSnake 325' (99 m) Self-Leveling Color Reel (PAL)	230	53.0	24.5

### Pipe Guides

Catalog No.	Description	Weight	
		lb.	kg
97832	75 mm Roller Dolly, Fits 35 mm Camera	-	-
64497	75 mm Centering Star Guide, Fits 35 mm Camera (pkg. of 20)	-	-
97852	85 mm Pipe Guide, Fits 35 mm Camera (pkg. of 10)	-	-
64502	150 mm Centering Star Guide, Fits 35 mm Camera (pkg. of 10)	-	-

### Accessories

Catalog No.	Description	Weight	
		lb.	kg
48548	Standard Camera head, Color, Self-Leveling (PAL)	-	-
15323	SeeSnake Standard Flexmitter	0.6	0.3
17563	Color Spanner Wrench	-	-
31753	Count Plus Cable Counter	-	-
64627	SeeSnake Interconnect Cord – 33/10' (10 m / 3 m)"	-	-
93387	SeeSnake Guide Hoop (pkg. of 4)	0.2	0.1

### Replacement Parts

Catalog No.	Description
35103	200' (61 m) SeeSnake Push Cable Assembly (Single Safety Cable)
35108	325' (99 m) SeeSnake Push Cable Assembly (Single Safety Cable)
64607	200' (61 m) Standard SeeSnake Push Cable Assembly
64612	325' (99 m) Standard SeeSnake Push Cable Assembly