Liberty Pumps

SPAC-Series



Assembled Sump Pump Package

Assembled sump pump system with 1/3 or 1/2 hp sump pump. Molded pump platform helps to secure pump and reduce potential jamming from debris.

Features:

- 1/3 or 1/2 hp sump pump
- 18" x 22" polyethylene sump pit and cover with gasket and hardware
- Pre-assembled with 1-1/2" Schedule 40 PVC discharge pipe
- Molded pump support platform raises pump off bottom of pit and helps secure pump during shipping
 - Two 4" inlet hubs with rubber grommet seals provided
 - Gasket sealed cover Radon readv

Models:

SPAC-237 1/3 hp. (model 237 sump pump) SPAC-S37 1/3 hp. (model \$37 sump pump) SPAC-S37-P 1/3 hp. (model S37-P sump pump) **SPAC-457** 1/2 hp. (model 457 sump pump)

innovate. evolve.

SPAC-SERIES

Assembled Sump Pump package


Pump Models Available:

SPAC-237 1/3 hp. Model 237, 115V., 5.2a, 60 Hz. SPAC-S37 1/3 hp. Model S37, 115V., 6.5a, 60 Hz. SPAC-S37-P 1/3 hp. Model S37-P, 115V., 6.5a, 60 Hz. (Piggy-back style float)

SPAC-457 1/2 hp. Model 457, 115V., 7.3a, 60 Hz.

For 25' cords on 237 or 457 models, add a "-2" suffix to model number. Example SPAC-237-2. See 230-Series, S30-Series or 450-Series literature for complete pump specifications.

SPAC-Series Performance Curve 60Hz



Dimensional Data

