

# SeeSnake® Wi-Fi Enabled Monitors and Recorders



## RIDGID® SEESNAKE CS65X DIGITAL REPORTING MONITOR

The SeeSnake CS65x digital reporting monitor has superior reporting capabilities. Directly capture inspection photos and videos on up to two USB drives as well as the CS65x's internal storage. The water-resistant, built-in keyboard and on-board reporting software lets you enhance captured media with overlaying notes and customer information right from the job site.

### FEATURES

- Dual USB ports give you the ability to make up to two copies of the job at once.
- Durable, internal solid-state storage device provides ample storage for multiple inspection jobs.
- Built-in Wi-Fi and Bluetooth allows live inspection streaming on an iOS or Android device with the free HQx® Live app.
- TiltSense™ displays the camera's degree of tilt from horizontal when connected to a SeeSnake camera reel with TruSense™.
- Integrated GPS allows media to be geo-referenced when GPS signal lock is available.
- Docks to the SeeSnake MAX™ rM200 reel for easy transport.

### SPECIFICATIONS

- Length – 16" (406 mm)
- Width – 12.5" (319 mm)
- Height – 9.5" (242 mm)
- Display – 6.5" (165 mm) Color LCD
- Display Resolution – 640 × 480 (VGA)
- Power Source – 18 V Advanced Lithium Battery or AC Power Cable
- Operating Temperature – 14°F to 122°F (-10°C to 50°C)
- Storage Temperature – -4°F to 140°F (-20°C to 60°C)
- Media Transfer – USB Drive or Wi-Fi via HQx Live
- Audio – Integrated Microphone and Speaker
- Autolog – MPEG4 (H.264)
- Photo Format – JPEG
- Video Format – MPEG4 (H.264)



SeeSnake rM200 with CS65x docked for easy transport

Catalog No.	Description	Weight	
		lb	kg
54363	CS65x Digital Reporting Monitor	9.3	4.2
55978	CS65x w/2 Batteries and 1 Charger	13.1	5
45363	AC Battery Adapter	1	0.5
44693	18 V Advanced Lithium 2.0 Ah Battery	1	0.5
44698	18 V Advanced Lithium 4.0 Ah Battery	1.5	0.7
43458	18 V Advanced Lithium Battery Charger	1.8	0.8

