Specialty Vacuums





14 GALLON WITH CERTIFIED HEPA FILTRATION

The RIDGID[®] Model RV2400HF professional wet dry vac is a 14-gallon, 2-stage wet dry vacuum with certified HEPA Filtration that meets EPA's definition under the RRP rule for lead paint renovations. It delivers the high-lift suction, large capacity, rugged construction for pro, contractor and industrial use.

- 11.5 Amp Motor Drives two blower wheels to optimize suction and deliver industry-leading performance.
- Longer Motor Life Over 700 hours on average.
- 2-Piece Polypropylene Drum Construction Rugged construction to meet the higher demands found at worksites
- 2-Stage Motor Creates powerful "high-lift" suction and more efficient air flow. Result more suction power and quieter operation.
- 3 Layers of Filtration Disposable high-efficiency filter bags collect larger debris. Then a washable fabric filter cover captures particles down to 0.5 microns. The certified HEPA filter then captures the smallest particulates down to 0.3 microns.
- Oversized Drain Large drain located at the lowest point of the drum for emptying of water.
- Sound Reduction Technology Scroll Noise Reduction[®] is a patented feature that provides quiet operation by precisely controlling the flow of air through the vac.
- Accessory Storage Bag Keeps accessories organized and close by for easy access.
- Cord-Wrap/Large Handle Large carry handle provides an area for the storage of the 25' power cord.
- Blowing Capacity Blow leaves from walkways or decks and debris from job sites, tools, etc.
- Professional Locking Hose The ultra-flexible hose won't pull loose during use, and is four times more durable than our standard hose. This 2-1/2"x 10' hose has a smooth interior surface to reduce clogging.
- Locking Accessories Included accessories lock together, so nothing falls off when in use.
- Qwik Lock[®] Filter Fastening System Install or remove your filter quickly, easily and secure without tools or fasteners.
- Includes Vacuum, owner's manual, 2 extension wands, 2 ½" x 10' premium locking pro hose, utility nozzle, wet nozzle, 14" floor brush, crevice tool, muffler/diffuser, filter bag, cloth pre-filter, certified HEPA filter, "beater bar" turbo brush with connector, and dusting brush.

SPECIFICATIONS

- Accessory Diameter 2 ¹/₂"
- Amperage 11.5A
- Built-In Accessory Storage Yes
- Built-In Drain Yes
- Casters Yes
- Filter Type HEPA Filter

	Catalog No. Mode	Model No.	Description	Cord Length	Air Volume	Shipping Weight
		would no.		ft.	(CFM)	lb.
	50368	RV2400HF	14 Gallon HEPA certified Wet/Dry Vac	25	105	37.7

