QS-style Copper Adapter

Submittal Information Revision B: July 22, 2010

Project Information

Job Name:


Location:	Part No. Ordered:	
Engineer:	Date Submitted:	
Contractor:	Submitted By:	
Manufacturer's Representative:	Approved By:	

Technical Data

Material:	CA 360 Brass
Maximum Temperature (no pressure):	220°F (104°C)
Maximum Pressure:	125 psi (8.6 bar)

Product Information and Application Use

The Uponor QS-style Copper Adapters, combined with the appropriate QS-style Fitting Assembly, transition Wirsbo hePEXTM or Uponor AquaPEX[®] tubing to $\frac{1}{2}$ " and $\frac{3}{4}$ " copper pipe in hydronic heating applications.



✓	Description	Part Number	Α	В	С	D	Weight
	QS-style Copper Adapter, R20 x $\frac{1}{2}$ " Copper	A4332050	1.30"	1.0625" HEX	R20	0.50" CU	0.14 lbs.
	QS-style Copper Adapter, R20 x 34 " Copper	A4332075	1.40"	1.0625" HEX	R20	0.75" CU	0.14 lbs.
	QS-style Copper Adapter, R25 x 34 " Copper (for 34 " and 56 " tubing only)	A4332575	1.94"	1.3750" HEX	R25	0.75" CU	0.30 lbs.

Installation

The corresponding compression fitting threads onto the R20 or R25 thread to adapt to copper. For additional information, refer to the Uponor Radiant Floor Heating Installation Handbook.

Standards

ASTM F877

Codes

R20: ISO 228-G 3/4 B; R25: ISO 222-G 1 B

Listings

NSF-rfh

Related Applications

Radiant Heating and Cooling Systems Snow and Ice Melting Systems Permafrost Protection Systems Turf Conditioning Systems

Contact Information

Uponor, Inc. 5925 148th Street West Apple Valley, MN 55124 USA Phone: (800) 321-4739 Fax: (952) 891-2008 www.uponor-usa.com Uponor Ltd. 2000 Argentia Rd., Plaza 1, Ste. 200 Mississauga, ON L5N 1W1 CANADA Phone: (888) 994-7726 Fax: (800) 638-9517 www.uponor.ca

uponor