

Hand-Held Video Inspection

RIDGID MICRO CA-150 INSPECTION CAMERA

The RIDGID micro CA-150 Inspection Camera allows you to perform more detailed visual inspections in even harder-to-reach areas.

FEATURES

- Comfortable one-hand grip for steady control while maneuvering camera.
- Large 3.5" color display allows fast diagnosis in tight hidden spaces.
- Illuminate dark areas with 4 bright LEDs on the waterproof camera head.
- Capture up to 20 still images during inspections to playback on screen later.

SPECIFICATIONS

- Display – 3.5" Color LCD (320 × 240 Resolution)
- Camera Head – 17 mm Aluminum
- Lighting – 4 LEDs with Adjustable Brightness
- Cable Reach – 3' (90 cm) (Expandable to 30' with optional extension)
- Internal Memory – 20 images
- Playback – On screen only
- Power Source – Batteries (4 × AA)
- Attachments – Mirror, Hook & Magnet
- Weight – 5.5 lb (2.5 kg)
- Waterproof – Camera Head and Cable to 10' (3 m) (when properly assembled)



Catalog No.	Description	Weight	
		lb	kg
36848	micro CA-150 Inspection Camera	5.5	2.5

Accessories

Catalog No.	Description	Weight	
		lb	kg
37108	3' (.91 m) Cable Extension	0.7	0.3
37113	6' (1.8 m) Cable Extension	1.4	0.8

Replacement Parts

Catalog No.	Description	Weight	
		lb	kg
37103	17 mm Replacement Imager	0.7	0.3

Hand-Held Video Inspection

RIDGID® MICRO CA-350 INSPECTION CAMERA

Inspection and documentation made easy with the new RIDGID micro CA-350 Inspection Camera, now with 12V power.

FEATURES

- Easily record still images and videos of problems in hard-to-reach areas.
- 12V rechargeable Lithium-Ion battery provides longer runtime for extended inspections.
- Comfortable pistol grip design, large screen, and easy-to-use interface.
- Illuminate dark spaces with four bright LEDs on the waterproof aluminum camera head.
- Get the perfect view with enhanced features like image rotation and digital zoom.

SPECIFICATIONS

- Display – 3.5" Color TFT
- Camera Diameter – 0.7" to 11/16" (17 mm)
- Lighting – 4 LEDs with adjustable brightness
- Cable Reach – 3' (90 cm) expandable to 30' (9 m) w/optional extensions, also compatible with microDrain, microReel and nanoReel
- Images – JPEG 640 × 480 Resolution
- Video – MP4 640 × 480 Resolution
- Power Source – Rechargeable 12V Li-Ion battery
- External Memory – SD Card up to 32 GB (8GB SD card included)

Catalog No.	Description	Weight	
		lb	kg
55898	micro CA-350 Inspection Camera	2.0	0.9

Included: micro CA-350 with 17 mm imager, battery, charger, USB cable, hook, magnet and mirror accessories, RCA cable, AC adapter, headset with microphone, 8GB SD card.

Accessories

Catalog No.	Description	Weight	
		lb	kg
37098	6 mm Imager with 1 m Cable*	0.2	0.1
37093	6 mm Imager with 4 m Cable*	0.9	0.4
37108	3' (.91 m) Cable Extension	0.7	0.3
37113	6' (1.8 m) Cable Extension	1.4	0.8

Replacement Parts

Catalog No.	Description	Weight	
		lb	kg
37103	17 mm Replacement Imager	0.7	0.3
37123	Mirror, Hook and Magnet for 17 mm Camera Head	0.1	0.0
55183	micro CA-350 12 V Li-Ion Battery	0.34	0.15

Compatible Camera Reels

Catalog No.	Description	Weight	
		lb	kg
39998	nanoReel N85S (micro CA-350) NTSC	11	5
37473	microDrain D65S Reel (CA-350) NTSC	9.8	4.4
35143	microReel L100 Reel (CA-350) NTSC	12	5.3

