

Halo SRL

GUARDIAN
FALL PROTECTION

Part #	Length	Description
10910	20'	3/16" Galvanized Cable w/Carabiner, Swivel Top, & Snap Hook
10912	25'	3/16" Galvanized Cable w/Carabiner, Swivel Top, & Snap Hook
10915	30'	3/16" Galvanized Cable w/Carabiner, Swivel Top, & Snap Hook
10930	20'	3/16" Stainless Steel Cable w/Carabiner, Swivel Top, & Snap Hook
10932	25'	3/16" Stainless Steel Cable w/Carabiner, Swivel Top, & Snap Hook
10935	30'	3/16" Stainless Steel Cable w/Carabiner, Swivel Top, & Snap Hook
10944	30'	3/16" Galvanized Cable w/Carabiner, Swivel Top, Non-Indicating Snap Hook, & Shock Pack



Compliant with all OSHA 1910, OSHA 1926 Subpart M, ANSI Z359.14-2014, and ANSI A10.32-2012 fall protection regulations.

Custom configurations available. Repairable by the manufacturer. Contact customer service for details.

Halo SRL is suitable for the following applications:



Personal Fall Arrest: Halo Series SRLs may be used in Personal Fall Arrest applications as a component of a MAXIMUM 1 Personal Fall Arrest System (PFAS). Structure must withstand loads applied in the directions permitted by the system of at least 5,000 lbs. No free fall is permitted. SRL must always be positioned at or above harness dorsal D-ring AND at or below anchor point. Applicable D-ring: Dorsal.



Restraint: Halo Series SRLs may be used in Restraint applications. Restraint systems prevent workers from reaching the leading edge of a fall hazard. Always account for fully deployed length of lanyard/SRL. Structure must withstand loads applied in the directions permitted by the system of at least 1,000 lbs. No free fall is permitted. Restraint systems may only be used on surfaces with slopes up to 4/12 (vertical/horizontal). Applicable D-rings: Dorsal, Chest, Side, Shoulder.

**For all applications, worker weight capacity range
(including all clothing, tools, and equipment): 130-310 lbs.**



WARNING Use of equipment in unintended applications may result in serious injury or death. Maximum 1 attachment per connection point.

Max. arresting distance: 54"

Min. fall clearance: 9'

Class B SRL

Materials: aluminum, galvanized steel, and stainless steel.

MAXIMUM 1 user per Halo SRL.