

## Seraph Harness

Part #	Sizes	Description
11140	S	Seraph Rescue/Retrieval Harness w/Shoulder D-rings
11141	M - L	Seraph Rescue/Retrieval Harness w/Side D-rings
11142	XL - XXL	Seraph Rescue/Retrieval Harness w/Side D-rings
11143	S	Seraph Rescue/Retrieval Construction Harness w/Shoulder & Side D-rings
11144	M - L	Seraph Rescue/Retrieval Construction Harness w/Shoulder & Side D-rings
11145	XL - XXL	Seraph Rescue/Retrieval Construction Harness w/Shoulder & Side D-rings
11160	M - L	Seraph Harness
11161	M - L	Seraph Harness w/Side D-Rings
11162	XL - XXL	Seraph Harness
11163	XL - XXL	Seraph Harness w/Side D-Rings
11164	M - XL	Seraph Harness w/Leg Tongue Buckles
11165	M - L	Seraph Harness w/Leg Tongue Buckles & Side D-Rings
11166	XL - XXL	Seraph Harness w/Leg Tongue Buckles
11170	M - L	Seraph Construction Harness
11171	XL - XXL	Seraph Construction Harness w/Side D-Rings
11172	XL - XXL	Seraph Construction Harness
11173	M - L	Seraph Construction Harness w/Side D-Rings
11174	S	Seraph Construction Harness w/Side D-Rings



Compliant with all OSHA 1910, OSHA 1926 Subpart M, ANSI Z359.1-2007, and ANSI A10.32-2012 regulations.

Seraph Harness is suitable for the following applications:



**Personal Fall Arrest:** Seraph Harness may be used in Personal Fall Arrest applications as a component of a Personal Fall Arrest System (PFAS). Structure must withstand loads applied in the directions permitted by the system of at least 5,000 lbs. Maximum free fall is 6', unless used in combination with equipment explicitly certified for extended free fall. Applicable D-ring: Dorsal.



**Restraint:** Seraph Harness may be used in Restraint applications. Restraint systems prevent workers from reaching the leading edge of a fall hazard. Always account for fully deployed length of lanyard/SRL. Structure must withstand loads applied in the directions permitted by the system of at least 1,000 lbs. No free fall is permitted. Restraint systems may only be used on surfaces with slopes up to 4/12 (vertical/horizontal). Applicable D-rings: Dorsal, Chest, Side, Shoulder.



**Work Positioning:** Seraph Harness, configured with side or shoulder D-rings, may be used in Work Positioning applications. Work Positioning systems allow a worker to be supported while in suspension and work freely with both hands. Structure must withstand loads applied in the directions permitted by the system of at least 3,000 lbs. Maximum allowable free fall is 2'. Applicable D-rings: Side.



**Rescue/Confined Space:** Seraph Harness may be used in Rescue/Confined Space applications. Rescue systems function to safely recover a worker from a confined location or after exposed to a fall. There are various configurations of Rescue systems depending on the type of rescue. Structure must withstand loads applied in the directions permitted by the system of at least 3,000 lbs. No free fall is permitted. Applicable D-rings: Dorsal, chest, shoulder.

**For all applications: worker weight capacity range (including all clothing, tools, and equipment) is 130-420 lbs.**

Materials: polyester and galvanized steel.

Always follow all manufacturer's instructions for proper adornment and use. Some steps of adorning a harness may require assistance from another person. Upon completely adorning a harness, Guardian Fall Protection recommends that another person, with knowledge of the safe and correct use of the harness, inspect to ensure the harness is being worn correctly.

Please contact Guardian Fall Protection for product-specific UPC codes.