



Amerex Corporation

RUGGED

- 6 Year Warranty
- Stored Pressure Design
- Dependable Drawn Steel Cylinders
- Durable High Gloss Polyester Powder Paint
- All Metal Valve Construction
- Temperature Range -65°F to 120°F

USER FRIENDLY

- Easy and More Economical to Maintain and Service
- Large Loop Pull Pin
- Bar Coded and Bi-lingual Labels

OPTION

- USCG Approved with Bracket Listed on UL Label



Aluminum Valve
 B417/T
 B500/T
 B402/T
 B443
 B456
 A411



Brass Valve
 B424
 B461
 B441
 423



Available in Wheeled and Stationary Extinguishers

ABC or Multi-Purpose extinguishers utilize a specially fluidized and siliconized mono ammonium phosphate dry chemical. It chemically insulates Class A fires by melting at approximately 350°F and coats surface to which it is applied. It smothers and breaks the chain reaction of Class B fires and will not conduct electricity back to the operator.

Largest selection of size and extinguisher options available

AGENT TYPE		ABC DRY CHEMICAL									
VALVE TYPE	ANODIZED ALUMINUM						CHROME PLATED BRASS				
DESIGN	NOZZLE	HOSE & NOZZLE				HOSE & NOZZLE					
MODEL NUMBER	B417/B417T	B500/B500T	B402/B402T	B443	B456	A411	B424	B461	B441	423	
UL & ULC RATING	1A:10B:C	2A:10B:C	3A:40B:C	3A:40B:C	4A:80B:C	10A:120B:C	2A:10B:C	3A:40B:C	4A:80B:C	10A:120B:C	
CAPACITY (LBS.)	2.5	5	5	6	10	20	5	6	10	20	
SHIPPING WT. (LBS.)	5.25/5.5	9.25/9.5	9.25/9.5	12.75	18	38	10.5	13.75	19	39	
HEIGHT (IN.)	15.5	15.25	15.25	16	20	24	15.5	16.25	20.5	24	
WIDTH (IN.)	5.75	7.25	7.25	7.75	7.75	10.25	8	8.5	8.75	10.25	
DEPTH (IN.)	3	4.25	4.25	5	5	7	4.25	5	5	7	
RANGE (INITIAL- FT)	9-15	12-18	12-18	15-21	15-21	15-21	12-18	15-21	15-21	15-21	
DISCHARGE TIME (SEC.)	10	14	14	14.5	20	30	14	14	20	30	
FM APPROVED	YES	YES	YES	YES		YES		YES		YES	
OPTIONAL CHROME CYLINDER	YES	YES	YES	YES	YES		YES	YES	YES		
INCLUDED BRACKET	WALL/VEHICLE			WALL	WALL		WALL				

Manufactured and Tested to ANSI/UL Standards
 Complies with NFPA 10 Standard
 ISO-9001 / ISO-14001 Certified
UL LISTED

CONFORMS TO TEST STANDARDS:

CAN/ULC-S504 - ANSI/UL299 &
 CAN/ULC-S508 - ANSI/UL711

MADE IN U.S.A.

AGENT TYPE	SIZE (CAPACITY)	MODEL	CYL. DIA. (INCH)	INCLUDED BRACKET	USCG BRACKET	OPTIONAL BRACKETS	RUBBER STRAP BRACKETS	859 DOLLY OPTION
WATER	2.5 GAL.	240	7	01007 WALL	N/A	810	864	YES
WATER MIST	1.75 GAL.	B270NM	7	14315 WALL	N/A	810NM	N/A	
	2.5 GAL.	B272NM	7	14135 WALL	N/A	810NM	N/A	
AFFFOAM	6 LITER	254	7	01007 WALL	N/A	810	864	
	2.5 GAL.	250	7	01007 WALL	N/A	810	864	YES
FFFOAM	2.5 GAL.	252	7	01007 WALL	N/A	810	864	YES
WET CHEMICAL	6 LITER	B260	7	01007 WALL	810	810	N/A	
	2.5 GAL.	B262	7	01007 WALL	810	810	N/A	YES
	6 LITER	B260CG	7	01007 WALL	810CG	N/A	N/A	
	2.5 GAL.	B262CG	7	01007 WALL	810CG	N/A	N/A	
HALOTRON® I	1.4 LB.	A384T	2.88	845 VEHICLE	N/A	N/A	N/A	
	2.5 LB.	B385TS	4.25	817S AIRCRAFT	N/A	817S	860	
	5 LB.	B386T	4.25	818 V/MARINE	818, 821, 861H	818S, 821, 821S, 807	860	
	5.5 LB.	B394TS	4.25	818S AIRCRAFT	N/A	N/A	N/A	
	11 LB.	397	6	00575 WALL	812	812	N/A	
	15.5 LB.	398	6	00575 WALL	812	812	N/A	
HALON 1211	1.25 LB.	A344T	2.88	845 VEHICLE	N/A	N/A	N/A	
	2.5 LB.	C352TS	3	817S AIRCRAFT	N/A	N/A	860	
	3 LB.	C354TS	3	817S AIRCRAFT	N/A	N/A	860	
	5 LB.	B355T	4.25	818 V/MARINE	818, 821, 861H	818S, 821, 821S, 807	860	
	9 LB.	B369	5	00546 WALL	808, 809	808, 809, 889HB	862	
	13 LB.	B371	5	01007 WALL	809	846, 809, 889HB	862	
ABC DRY CHEMICAL	17 LB.	361	7	00577 WALL	810	810	864	YES
	2.5 LB.	B417 / B417T	3	4834 WALL / 817 VM	817	817S	860	
	5 LB.	B402 / B402T	4.25	16591 WALL / 818 VM	818, 821, 861H	818S, 821, 821S, 807	862	
	5 LB.	B500 / B500T	4.25	16591 WALL / 818 VM	818, 821, 861H	818S, 821, 821S, 807	862	
	5 LB.	B424	4.25	16591 WALL	821, 861H	821, 821S, 807	862	
	6 LB.	B443	5	00525 WALL	808, 809, 895	808, 809, 889, 895	862	
	6 LB.	B461	5	00546 WALL	808, 809, 895	808, 809, 889, 895	862	
	10 LB.	B456	5	00546 WALL	808, 809, 895	808, 809, 889, 889HB, 895	862	
	10 LB.	B441	5	01007 WALL	809, 895	808, 809, 889HB, 895	862	
	20 LB.	A411	7	00577 WALL	810	810	864	YES
REGULAR DRY CHEMICAL	20 LB.	423	7	00577 WALL	810	810	864	YES
	1 LB.	A620T	2.88	845 VEHICLE	N/A	N/A	N/A	
	2.5 LB.	B403 / B403T	3	4834 WALL / 817 VM	817	817S	860	
	5 LB.	B409T	4.25	818 V/MARINE	818, 821, 861H	807, 818, 821, 861H	862	
	5.5 LB.	B453	4.25	16591 WALL	818, 821, 861H	807, 818, 821, 861H	862	
	6 LB.	B462	5	00546 WALL	808, 809, 895	808, 809, 889HB, 895	862	
	10 LB.	B447	5	01007 WALL	809, 895	809, 846, 889HB, 895	862	
	10 LB.	B457	5	00546 WALL	809, 895	809, 846, 889HB, 895	862	
	20 LB.	A412	7	00577 WALL	810	810	864	YES
	20 LB.	408	7	00577 WALL	810	810	864	YES
PURPLE K DRY CHEMICAL	2.5 LB.	B410T	3	817 V/MARINE	817	817S	860	
	5 LB.	B479 / B479T	4.25	16591 WALL / 818 VM	818, 821, 861H	807, 818S, 821, 821S, 861H	860	
	10 LB.	B460	5	01007 WALL	809, 895	809, 846, 889HB	862	
	20 LB.	A413	7	00577 WALL	810	810	864	YES
	20 LB.	415	7	00577 WALL	810	810	864	YES
CARBON DIOXIDE	5 LB.	322	5.25	00546 WALL	809	809	862	
	5 LB.	322NM	5.25	17737 WALL	N/A	N/A	N/A	
	10 LB.	330	7	00575 WALL	810	810	N/A	
	15 LB.	331	7	00575 WALL	810	810	864	YES
	20 LB.	332	8	00577 WALL	811	811	864	YES
HIGH PERFORMANCE DRY CHEMICAL <i>FAST FLOW AND COMPLIANCE FLOW</i>	13.2 LB. (6 KG)	594, 592, 595, 599	7	09582 WALL	810 & 810G	810 & 810G	N/A	
	20 LB. (9 KG)	581, 582, 580, 584, 564, 566	7	09852 WALL	810 & 810G	810 & 810G	864 & 874	YES
	30 LB. (13.6 KG)	567, 568, 569, 589, 591	7	09581 WALL	811 & 811G	811 & 811G	864	YES
HIGH FLOW EXTINGUISHERS	10 LB.	720, 721, 722	5	01007 WALL	809, 895	808, 809, 889HB, 895	862	
	20 LB.	760, 761, 762	7	00577 WALL	810	810	864	YES
CLASS D DRY POWDER	30 LB.	B570	8	00577 WALL	N/A	811	864	YES
	30 LB.	B571	8	00577 WALL	N/A	811	864	YES

All Amerex brackets are quality made and manufactured of steel with a powder coated paint. The paint finish assures many years of use and meets the latest UL salt spray requirements (240 hrs. @ 20% salt solution - ASTM B117).