

aquatherm green pipe® SDR 7.4 MF UV

Material: fusiolen® PP-R multi-layer, fiber-composite

In accordance with:

- NSF-14
- NSF-51
- NSF-61
- CSA-B137.11
- ICC AC 122
- ICC ESR 1613
- ASTM F 2389
- CFIA #A508




Appearance: Light green with black exterior.

NSF system certification: Including fittings, connection pieces and connection techniques.

Fields of application: All the same applications as the standard aquatherm green pipe® SDR 7.4 MF, but for installations where the pipe is exposed to UV radiation.

Note: Because these parts are not stocked in large numbers, please contact Aquatherm for details about your order. Pipe will not have NA listing marks on it, but can be special ordered with the marking.



Pipe ^a		Diameter ^b	Wall thickness	Internal diameter	(d) total	Water capacity	Weight ^c	Weight w/ water
Part no.	Dimension (ND — OD)	d (in)	s (in)	d _i (in)	d _g (in)	gal/ft	lb/ft	lb/ft
0670758	½" — 20 mm	0.79	0.11	14.4	0.87	0.013	0.14	0.25
0670760	¾" — 25 mm	0.98	0.14	18.0	1.06	0.021	0.21	0.38
0670762	1" — 32 mm	1.26	0.17	23.2	1.34	0.034	0.33	0.60
0670764	1 ¼" — 40 mm	1.57	0.22	29.0	1.65	0.054	0.49	0.92
0670766	1 ½" — 50 mm	1.97	0.27	36.2	2.05	0.084	0.74	1.41
0670768	2" — 63 mm	2.48	0.34	45.8	2.56	0.134	1.14	2.20
0670770	2 ½" — 75 mm	2.95	0.41	54.4	3.03	0.189	1.59	3.09
0670772	3" — 90 mm	3.54	0.48	65.4	3.62	0.273	2.28	4.46
0670774	3 ½" — 110 mm	4.33	0.59	79.8	4.45	0.407	3.42	6.66
0670776	4" — 125 mm	4.92	0.67	90.8	5.00	0.526	4.33	8.53
0670780	6" — 160 mm	6.30	0.86	116.2	6.38	0.826	7.00	13.9
0670784	8" — 200 mm	7.87	1.08	145.2	7.95	1.347	10.8	21.7
0670788	10" — 250 mm	9.84	1.35	181.6	9.92	2.105	16.8	34.0

^a Pipes come in standard 19 ft lengths (5.8 m).

^b To calculate dimensions of the pipe in millimeters, multiply the imperial inches measurement by 25.4.

^c To calculate the weight of the pipe in kg/m, multiply the measurement by 1.5.



aquatherm

we've got a pipe for that