

# Lovibond® Water Testing Tintometer® Group



## MD 100 Phosphate, powder reagents

Precise Water Analysis in High-Quality Design



- Lightweight, rugged design for use in the field
- Single unit construction with no parts to lose or break
- Large, easy to read display
- Industry specific parameter combinations available

Part Number: 276045

The MD 100 has several key features that make it a favorite among users.

### Waterproof Design

The IP 68 design of this instrument ensures that the MD 100 remains water tight for up to 1 hour at 0.1 meter. Don't worry about dropping the instrument into a body of water - it floats!

### Accurate, Reproducible Results

The optical system of the MD 100 utilizes LEDs and interference filters which quickly gives you results that you can be confident in.

### User Calibration Mode

A one-point calibration is possible. Additionally, all MD 100 instruments have the ability to display readings directly in ABS or %T units.

### One-time-Zero Function

Don't waste time waiting for your instrument to Zero after each test. When testing a new sample, zero the instrument once and all subsequent tests of that sample do not require you to re-zero the instrument.

### Automatic Data Storage with Transfer Capabilities

The MD 100 automatically stores the last 16 readings with time and date stamp. These results can be transferred to a spreadsheet using the IRIIM accessory.

### Ergonomic Design

Whether you're using the MD 100 out in the field or in the lab, the design of the instrument makes it easy to handle and view the display. If you're using the instrument in the lab, the rubber feet on

the bottom of the housing eliminates the need for two hand operation or to chase your instrument around the workbench.

### Factory Programmed

All MD 100 instruments are supplied ready to use with up to 14 calibration curves. All you need to do is select the test you need, prepare your sample and test!

### Scroll Driven Menu System

The simple interface allows you to quickly reach the test you need. When the instrument is turned on, it will automatically display the last test used.

### 2-Year Manufacturer's Warranty

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Power and Energy

Application

Boiler Water | Drinking Water Treatment | Pool Water Control | Raw Water Treatment | Waste Water Treatment

MD 100 Phosphate, powder reagents

The MD 100 is a single parameter colorimeter for water quality analysis. The rugged design makes this instrument completely portable and ideal for field use.

Ortho Phosphate is a common test in a variety of municipal water, wastewater and industrial applications. This instrument is pre-programmed with two testing ranges. Choose between using Lovibond® Tablet reagents or VARIO Powder Pack Reagents, depending on the range selected.

Measuring Range

| Test Name    | Measuring Range   | Chemical Method        |
|--------------|-------------------|------------------------|
| Phosphate PP | 0.02 - 0.8 mg/l P | Phosphomolybdenum Blue |

Technical Data

|                     |   |
|---------------------|---|
| Optics              | LEDs, interference filters (IF) and photo sensor in transparent sample chamber. Depending on the version, up to 3 different interference filters are used. Wavelength specifications of interference filters:<br>430 nm Δλ = 5 nm<br>530 nm Δλ = 5 nm<br>560 nm Δλ = 5 nm<br>580 nm Δλ = 5 nm<br>610 nm Δλ = 6 nm<br>660 nm Δλ = 5 nm |
| Wavelength Accuracy | ± 1   |
| Photometric Range   | -2500 - 2500 mAbs   |
| Operation           | Foil keypad   |
| Display             | backlit LCD (on keypress)   |
| Suitable Vials      | Round Cuvettes 24 mm  |
| Calibration         | factory calibration and user calibration. Reset to factory calibration possible   |
| Interfaces          | Infrared  |
| Internal Storage    | internal ring memory for 16 data sets   |
| Power Supply        | 4 micro batteries (AAA)   |
| Battery Life Time   | approx. 17 hours  |
| Auto – OFF          | Yes   |
| Clock               | Real Time Clock and Date  |
| Portability         | Portable  |
| Compliance          | CE  |
| Protection Class    | IP 68   |
| Dimensions          | 6.1 x 2.95 x 1.38"  |
| Weight              | 260 g   |

Delivery Scope

- Instrument in plastic case
- VARIO Phosphate RGT Powder Reagent
- 4 micro batteries (AAA)
- 3 round cuvettes (glass) with lid
- Sealing rings
- Stirring rod
- Brush
- Instruction manual
- Quick Start Guide
- Certificate (COC)
- Warranty information

Accessories

| Title   | Part Number |
|---|-------------|
| Water sampler, AF 631   | 170500      |
| Micro batteries (AAA), set of 4   | 1950026     |
| Multy cuvette-2, set of 12  | 197600      |
| Round cuvette 24 mm, set of 12  | 197620      |
| Sealing ring for round vials 24 mm, set of 12   | 197626      |
| Round cuvette 24 mm, set of 5   | 197629      |
| Cleaning cloth  | 197635      |
| Round cuvette 16 mm, set of 10  | 197665      |
| Adapter for round cuvettes 16 mm  | 19802190    |
| Mixing cylinder, 25 ml  | 19802650    |
| Infrared data transmission modul IRIiM  | 214050      |
| Verification Standard Kit MD 100 / 200  | 215670      |
| Stirring rod, 13 cm length  | 364100      |
| Stirring rod, 10 cm length  | 364109      |
| Stirring rod, 13 cm length, set of 10   | 364120      |
| Stirring rod, 10 cm length, set of 10   | 364130      |
| Membrane filter set for use when preparing samples, 25 membrane filters 0.45 µm, 2 syringes 20 ml | 366150      |
| 500 ml bottle, AF 631   | 375069      |
| Brush, 11 cm length   | 380230      |
| Measuring beaker, 100 ml  | 384801      |
| Cuvette stand for 6 round cuvettes Ø 24 mm  | 418951      |
| Cuvette stand for 10 round cuvettes Ø 16 mm   | 418957      |
| Plastic funnel with handle (white)  | 471007      |
| Basic price for calibration certificate for each unit   | 999845      |
| Additionally for each method  | 999855      |

---

**Tintometer GmbH**

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
Fax: +49 (0)231/94510-30  
sales@lovibond.com  
www.lovibond.com  
Germany

**Tintometer China**

Room 1001, China Life Tower  
16 Chaoyangmenwai Avenue,  
Beijing, 100020  
Tel.: +86 10 85251111 App. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

**Tintometer Inc.**

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.com  
USA

**The Tintometer Limited**

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

**Tintometer South East Asia**

Unit B-3-12, BBT One Boulevard,  
Lebu Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

**Tintometer India Pvt. Ltd.**

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@tintometer.com  
www.lovibondwater.in  
India

**Tintometer AG**

Hauptstraße 2  
5212 Hausen AG  
Tel.: +41 (0)56/4422829  
Fax: +41 (0)56/4424121  
info@tintometer.ch  
www.tintometer.ch  
Switzerland

**Tintometer Brazil**

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@tintometer.com.br  
www.lovibond.com.br  
Brazil

**Tintometer Spain**

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain