

Lovibond® Water Testing Tintometer® Group



MD 100 Ammonia, tablet reagents

Precise Water Analysis in High-Quality Design



- Lightweight, rugged design for use in the field
- Single unit construction with no parts to lose or break
- Large, easy to read display
- Industry specific parameter combinations available

Part Number: 276060

The MD 100 has several key features that make it a favorite among users.

Waterproof Design

The IP 68 design of this instrument ensures that the MD 100 remains water tight for up to 1 hour at 0.1 meter. Don't worry about dropping the instrument into a body of water - it floats!

Accurate, Reproducible Results

The optical system of the MD 100 utilizes LEDs and interference filters which quickly gives you results that you can be confident in.

User Calibration Mode

A one-point calibration is possible. Additionally, all MD 100 instruments have the ability to display readings directly in ABS or %T units.

One-time-Zero Function

Don't waste time waiting for your instrument to Zero after each test. When testing a new sample, zero the instrument once and all subsequent tests of that sample do not require you to re-zero the instrument.

Automatic Data Storage with Transfer Capabilities

The MD 100 automatically stores the last 16 readings with time and date stamp. These results can be transferred to a spreadsheet using the IRiM accessory.

Ergonomic Design

Whether you're using the MD 100 out in the field or in the lab, the design of the instrument makes it easy to handle and view the display. If you're using the instrument in the lab, the rubber feet on

the bottom of the housing eliminates the need for two hand operation or to chase your instrument around the workbench.

Factory Programmed

All MD 100 instruments are supplied ready to use with up to 14 calibration curves. All you need to do is select the test you need, prepare your sample and test!

Scroll Driven Menu System

The simple interface allows you to quickly reach the test you need. When the instrument is turned on, it will automatically display the last test used.

2-Year Manufacturer's Warranty

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry

Application

Drinking Water Treatment | Raw Water Treatment | Waste Water Treatment

MD 100 Ammonia, tablet reagents

The MD 100 is a single parameter colorimeter for water quality analysis. The rugged design makes this instrument completely portable and ideal for field use.

This instrument features two testing ranges and methods for testing Ammonia. Choose between using Lovibond® Tablet reagents or VARIO Powder Pack Reagents, depending on the range selected.

Measuring Range

Test Name	Measuring Range	Chemical Method
Ammonia T	0.02 - 1 mg/l N	Indophenole Blue

Technical Data

Optics	LEDs, interference filters (IF) and photo sensor in transparent sample chamber. Depending on the version, up to 3 different interference filters are used. Wavelength specifications of interference filters: 430 nm $\Delta\lambda = 5$ nm 530 nm $\Delta\lambda = 5$ nm 560 nm $\Delta\lambda = 5$ nm 580 nm $\Delta\lambda = 5$ nm 610 nm $\Delta\lambda = 6$ nm 660 nm $\Delta\lambda = 5$ nm
Wavelength Accuracy	± 1
Photometric Range	-2500 - 2500 mAbs
Operation	Foil keypad
Display	backlit LCD (on keypress)
Suitable Vials	Round Cuvettes 24 mm
Calibration	factory calibration and user calibration. Reset to factory calibration possible
Interfaces	Infrared
Internal Storage	internal ring memory for 16 data sets
Power Supply	4 micro batteries (AAA)
Battery Life Time	approx. 17 hours
Auto - OFF	Yes
Clock	Real Time Clock and Date
Portability	Portable
Compliance	CE
Protection Class	IP 68
Dimensions	6.1 x 2.95 x 1.38"
Weight	260 g

Delivery Scope

- Instrument in plastic case
- 100 tablet reagents Ammonia No.1
- 100 tablet reagents Ammonia No.2
- 4 micro batteries (AAA)
- 3 round cuvettes (glass) with lid
- Sealing rings
- Stirring rod
- Brush
- Instruction manual
- Quick Start Guide
- Certificate (COC)
- Warranty information

Accessories

Title	Part Number
Water sampler, AF 631	170500
Micro batteries (AAA), set of 4	1950026
Multy cuvette-2, set of 12	197600
Round cuvette 24 mm, set of 12	197620
Sealing ring for round vials 24 mm, set of 12	197626
Round cuvette 24 mm, set of 5	197629
Cleaning cloth	197635
Round cuvette 16 mm, set of 10	197665
Adapter for round cuvettes 16 mm	19802190
Mixing cylinder, 25 ml	19802650
Infrared data transmission modul IRiM	214050
Verification Standard Kit MD 100 / 200	215670
Stirring rod, 13 cm length	364100
Stirring rod, 10 cm length	364109
Stirring rod, 13 cm length, set of 10	364120
Stirring rod, 10 cm length, set of 10	364130
Membrane filter set for use when preparing samples, 25 membrane filters 0.45 μ m, 2 syringes 20 ml	366150
500 ml bottle, AF 631	375069
Brush, 11 cm length	380230
Measuring beaker, 100 ml	384801
Cuvette stand for 6 round cuvettes \varnothing 24 mm	418951
Cuvette stand for 10 round cuvettes \varnothing 16 mm	418957
Plastic funnel with handle (white)	471007
Basic price for calibration certificate for each unit	999845
Additionally for each method	999855

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
Fax: +49 (0)231/94510-30
sales@lovibond.com
www.lovibond.com
Germany

Tintometer China

Room 1001, China Life Tower
16 Chaoyangmenwai Avenue,
Beijing, 100020
Tel.: +86 10 85251111 App. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.com
USA

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebu Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@tintometer.com
www.lovibondwater.in
India

Tintometer AG

Hauptstraße 2
5212 Hausen AG
Tel.: +41 (0)56/4422829
Fax: +41 (0)56/4424121
info@tintometer.ch
www.tintometer.ch
Switzerland

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@tintometer.com.br
www.lovibond.com.br
Brazil

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain