

Product Specification

Tensar Biaxial Geogrid

- **Biaxial Geogrid BX1100**
- **Biaxial Geogrid BX1120**
- **Biaxial Geogrid BX1200**
- **Biaxial Geogrid BX1220**
- **Biaxial Geogrid BX1300**
- **Biaxial Geogrid BX1500**
- **Biaxial Geogrid BX4100**
- **Biaxial Geogrid BX4200**

Product Specification - Biaxial Geogrid BX1200

Tensar International Corporation reserves the right to change its product specifications at any time. It is the responsibility of the specifier and purchaser to ensure that product specifications used for design and procurement purposes are current and consistent with the products used in each instance.

Product Type: Integrally Formed Biaxial Geogrid
Polymer: Polypropylene
Load Transfer Mechanism: Positive Mechanical Interlock
Primary Applications: Spectra System (Base Reinforcement, Subgrade Improvement)

Product Properties

Index Properties	Units	MD Values ¹	XMD Values ¹
▪ Aperture Dimensions ²	mm (in)	25 (1.0)	33 (1.3)
▪ Minimum Rib Thickness ²	mm (in)	1.27 (0.05)	1.27 (0.05)
▪ Tensile Strength @ 2% Strain ³	kN/m (lb/ft)	6.0 (410)	9.0 (620)
▪ Tensile Strength @ 5% Strain ³	kN/m (lb/ft)	11.8 (810)	19.6 (1,340)
▪ Ultimate Tensile Strength ³	kN/m (lb/ft)	19.2 (1,310)	28.8 (1,970)
Structural Integrity			
▪ Junction Efficiency ⁴	%	93	
▪ Flexural Stiffness ⁵	mg-cm	750,000	
▪ Aperture Stability ⁶	m-N/deg	0.65	
Durability			
▪ Resistance to Installation Damage ⁷	%SC / %SW / %GP	95 / 93 / 90	
▪ Resistance to Long Term Degradation ⁸	%	100	
▪ Resistance to UV Degradation ⁹	%	100	

Dimensions and Delivery

The biaxial geogrid shall be delivered to the jobsite in roll form with each roll individually identified and nominally measuring 3.0 meters (9.8 feet) or 4.0 meters (13.1 feet) in width and 50.0 meters (164 feet) in length. A typical truckload quantity is 160 to 210 rolls.

Notes

1. Unless indicated otherwise, values shown are minimum average roll values determined in accordance with ASTM D4759-02. Brief descriptions of test procedures are given in the following notes.
2. Nominal dimensions.
3. Determined in accordance with ASTM D6637-10 Method A.
4. Load transfer capability determined in accordance with ASTM D7737-11.
5. Resistance to bending force determined in accordance with ASTM D7748-12, using specimens of width two ribs wide, with transverse ribs cut flush with exterior edges of longitudinal ribs, and of length sufficiently long to enable measurement of the overhang dimension.
6. Resistance to in-plane rotational movement measured by applying a 20 kg-cm (2 m-N) moment to the central junction of a 9 inch x 9 inch specimen restrained at its perimeter in accordance with GRI GG9.
7. Resistance to loss of load capacity or structural integrity when subjected to mechanical installation stress in clayey sand (SC), well graded sand (SW), and crushed stone classified as poorly graded gravel (GP). The geogrid shall be sampled in accordance with ASTM D5818 and load capacity shall be determined in accordance with ASTM D6637.
8. Resistance to loss of load capacity or structural integrity when subjected to chemically aggressive environments in accordance with EPA 9090 immersion testing.
9. Resistance to loss of load capacity or structural integrity when subjected to 500 hours of ultraviolet light and aggressive weathering in accordance with ASTM D4355-05.