

# Mirafi<sup>®</sup> S1200



Mirafi<sup>®</sup> S1200 is a needlepunched nonwoven geotextile composed of polypropylene fibers, which are formed into a stable network such that the fibers retain their relative position. Mirafi<sup>®</sup> S1200 is inert to biological degradation and resists naturally encountered chemicals, alkalis, and acids.

TenCate Geosynthetics Americas Laboratories are accredited by Geosynthetic Accreditation Institute – Laboratory Accreditation Program (GAI-LAP).

Mechanical Properties	Test Method	Unit	Minimum Average Roll Value
Weight	ASTM D5261	oz/yd <sup>2</sup> (g/m <sup>2</sup> )	12.0 (407)
Thickness	ASTM D5199	mils (mm)	130 (3.3)
Grab Tensile Strength	ASTM D4632	lbs (N)	320 (1424)
Grab Tensile Elongation	ASTM D4632	%	50
Trapezoid Tear Strength	ASTM D4533	lbs (N)	125 (556)
CBR Puncture Strength	ASTM D6241	lbs (N)	900 (4005)
			<b>Maximum Opening Size</b>
Apparent Opening Size (AOS)	ASTM D4751	U.S. Sieve (mm)	100 (0.15)
			<b>Minimum Roll Value</b>
Permittivity	ASTM D4491	sec <sup>-1</sup>	0.9
Permeability	ASTM D4491	cm/sec	0.3
Flow Rate	ASTM D4491	gal/min/ft <sup>2</sup> (l/min/m <sup>2</sup> )	65 (2648)
			<b>Minimum Test Value</b>
UV Resistance (at 500 hours)	ASTM D4355	% strength retained	80

Physical Properties	Unit	Roll Size
Roll Dimensions (width x length)	ft (m)	15 x 300 (4.5 x 91)
Roll Area	yd <sup>2</sup> (m <sup>2</sup> )	500 (418)

**Disclaimer:** TenCate assumes no liability for the accuracy or completeness of this information or for the ultimate use by the purchaser. TenCate disclaims any and all express, implied, or statutory standards, warranties or guarantees, including without limitation any implied warranty as to merchantability or fitness for a particular purpose or arising from a course of dealing or usage of trade as to any equipment, materials, or information furnished herewith. This document should not be construed as engineering advice.

Mirafi<sup>®</sup> is a registered trademark of Nicolon Corporation.

Copyright © 2013 Nicolon Corporation. All Rights Reserved.

365 South Holland Drive  
Pendergrass, GA 30567

Tel 706 693 2226  
Tel 888 795 0808

Fax 706 693 4400  
[www.tencate.com](http://www.tencate.com)

FGS000386  
ETQR13



GAI-LAP-25-97