



## FEATURES

- Energy Savings of up to 85%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Alabaster Glass with Steel Trim in Oil-Rubbed Bronze Finish
- Die Formed of 22 Gauge Plated Steel
- Replaces 2 x 60W Incandescent
- Dimmable

## APPLICATIONS

- Hallways
- Bedrooms
- Lobbies

## CERTIFICATIONS

- UL/cUL Listed
- Energy Star

## SPECIFICATIONS

Part Number: **LED1102-34-2CCT**

**Manufacturer Limited Warranty:** 3 Years  
**Kelvin Temperature (CCT):** 3000K or 4000K  
**Wattage:** 18.6  
**Lumens:** 1,103  
**Efficacy:** 59.3 lm/w  
**CRI:** 80  
**Dimmable:** 0-10V Dimming  
**Input Voltage:** DC 120V

**Certifications:** UL Listed

**DLC Listed:** No

**Average Hour Life:** 50,000 hrs

**Max. Ambient Temperature:** 45°C

**Min. Ambient Temperature:** -20°C

**Power Factor:** >0.9

**THD:** <20%

## TECHNICAL

**Weight:** 4.11 lbs

**Length:** 13.5"

**Product Height:** 4"

**Product Width:** 13.5"

**LED Beam Angel:** 120

**LED Type:** Integrated LED Array





Project:	<input type="text"/>	Date:	<input type="text"/>
Prepared by:	<input type="text"/>		
Comments	<input type="text"/>		

LINE DRAWINGS

