

UNDERGROUND CUTTING



CHAIN SAWS

U.S.SAWS offers a variety of chainsaw chains and bars to meet your cutting needs for the perfect combination of accuracy, productivity, and safety. The U.S.SAWS' chainsaws offer exceptional flexibility not frequently identified in most other brands of cutting tools. We offer the safest and most efficient way to cut through utility pipes.

Features: Pipe Cutting

- Deep cutting - one sided access
- No kickback
- No exhaust fumes
- Not effected by water in the cut

Features: Concrete Cutting

- Ideal for square corners
- Wet cutting reduces hazardous dust



AIR CHAIN SAW MODEL ACH-GB16

PART NUMBER: US60466

This air powered chain saw requires 90cfm of air at 90psi. The special PowerGrit chain allows the Model ACH-GB16 Air Powered Chain Saw to safely and quickly cut ductile iron, PVC, HDPE, and other similar materials.

Power Source	Gearbox Air Motor
Guide Bar	16" or 20"
Weight	27 lbs (With Bar and Chain)

AIR



GAS CHAIN SAW MODEL 695XL-16 F4

PART NUMBER: US71021

This gas powered chain saw is the highest horsepower ICS gas saw in the construction industry. Features includes Polyester air filter designed specifically for wet cutting. Available with 12"-16" guidebars. Recommended use for general construction, utility contractors and concrete professionals.

Power Source	2-Stroke Gas
Guide Bar	16"
Weight	28 lbs (With Bar and Chain)

GAS



HYDRAULIC CHAIN SAW MODEL 890F4

PN: US72000 (8 GPM-16")

PN: US72010 (12 GPM-16")

This hydraulic powered chain saw can be equipped with 16" or 20" Powergrit Chain & Guidebar which allows to safely and quickly cut ductile iron pipes and other similar materials.

Power Source	Hydraulic (8GPM or 12 GPM)
Guide Bar	16" or 20"
Weight	27.3 lbs (With Bar and Chain)

HYDRAULIC