



DUCT TAPE

Description

PROSELECT Duct Tapes are designed to answer your need for an economical general purpose duct tape. Made from high quality polyester (PET) cloth, polyethylene (PE) film, & a natural rubber, pressure sensitive adhesive. This results in a quality, general purpose duct tape.

Features

- With the grain or across the grain, PROSELECT duct tapes tear evenly and shred minimally.
- Excellent conformability to irregular surfaces.
- · Won't twist or curl during application

Common Applications

Packaging, wrapping, sealing & waterproofing, seaming, binding & bundling, and general maintenance & repair

Storage Conditions

Product should be stored in a cool, dry area in original packaging.

Government Compliance

- Tested in accordance with UL-723.
- HUD & BOCA rated

Codes

PSDTC260B	2" X 60yds	Premium Grade	Black
PSDTC260S	2" X 60yds	Premium Grade	Silver
PSDTC260CAMO	2" X 60yds	Utility Grade	Camouflage
PSDTU260S	2" X 60yds	Utility Grade	Silver



Quality	Utility Grade (PSDTU)	Premium Grade (PSDTC)	
Adhesive	Natural rubber	Natural rubber	
Carrier/Backing	Polyethylene coated cloth	Polyethylene coated cloth	
Total Thickness	8 mils	10 mils	
Adhesion to stainless steel (ounce per inch of width)	41	50	
Adhesion to Backing (ounce per inch of width)	45	45	
Tensile Strength (pounds per inch of width)	17	20	
Elongation (at break)	15%	18%	
Service/Operating Temperature	32°F to 200°F	32°F to 200°F	
Flame Spread Index	10	10	
Smoke Development Index	15	15	
VOC Content	< 0.1 g/L	< 0.1 g/L	
	UL723	UL723	
Certifications	HUD & BOCA Rated	HUD & BOCA Rated	
	LEED - contributes toward satisfying EQ Credit 4.1	LEED - contributes toward satisfying EQ Credit 4.1	

