ProPEX® EP Plug

uponor

Submittal Information Revision A: Feb. 27, 2009

Project Information

Job Name:

Location:	Part No. Ordered:		
Engineer:	Date Submitted:		
Contractor:	Submitted By:		
Manufacturer's Representative:	Approved By:		

Technical Data

Material: UDEL Polysulfone, 20% Glass-reinforced


(½" - 1"); Acudel Polysulfone (1¼" - 2")

Maximum Temperature

(no pressure): 320°F (160°C)

Maximum Working

Temperature/Pressure: 210°F (99°C) at 150 psi



Product Information and Application Use

ProPEX® EP Plugs are available for use in hot and cold domestic potable water systems. Plugs are also approved for use in any hydronic heating system. ProPEX EP Plugs temporarily or permanently terminate Uponor PEX tubing ends.

/ Description	Part Number	Α	В	Weight
ProPEX EP Plug for 1/2" PEX	Q4350500	0.850"	0.836"	0.006 lbs.
ProPEX EP Plug for ¾" PEX	Q4350750	0.850"	0.836"	0.008 lbs.
Propex EP Plug for 1" PEX	Q4351000	1.08"	1.187"	0.020 lbs.
ProPEX EP Plug for 11/4" PEX	Q4351250	1.32"	1.35"	0.040 lbs.
ProPEX EP Plug for 1½" PEX	Q4351500	2.00"	2.125"	0.075 lbs.
ProPEX EP Plug for 2" PEX	Q4352000	2.40"	2.625"	0.156 lbs.

Use the appropriate ProPEX Ring for PEX tubing. Refer to the AquaPEX® Professional Plumbing Installation Handbook or Uponor Radiant Installation Handbook for additional information.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

IAPMO 3558; ANSI/NSF 14- and 61-certified; HUD MR 1269; ICC ESR 1099

Related Applications Contact Information PEX-a Plumbing Systems Uponor, Inc. Uponor Ltd. 5925 148th Street West Radiant Heating and Cooling Systems 2000 Argentia Rd., Plaza 1, Ste. 200 Apple Valley, MN 55124 USA Mississauga, ON L5N 1W1 CANADA Phone: (800) 321-4739 Phone: (888) 994-7726 Fax: (952) 891-2008 Fax: (800) 638-9517 www.uponor-usa.com www.uponor.ca

 $^{^{1}}$ ProPEX $^{®}$ is a registered trademark of Uponor, Inc. ProPEX $^{™}$ is a trademark of Uponor Ltd.