





Ref. No.	Description	Material	Qty
1	Body	ASTM A351 Gr. CF8M	1
2	Ball	ASTM A351 Gr. CF8M	1
3	End Cap	ASTM A351 Gr. CF8M	1
4	Seat	RTFE	2
5	Body Seal	PTFE	1
6	Stem	316SS	1
7	Stem Packing	PTFE	1 Set
8	Handle	FCD45	1
9	Handle Cover	Vinyl	2
10	Thrust Washer	PTFE	1
11	Gland Nut/Bolt	304SS	1
11A	Follower	304SS	1
11B	Gland	CF8	1
12	Handle Washer	304SS	1
13	Handle Nut	304SS	2
13A	Handle Bolt	304SS	2
14	Locking Pad	304SS	1
16	Belleville Washer	301SS	2
17	Body Bolt/Stud	ASTM A193 Gr. B8	4-8
18	Body Nut	ASTM A194 Gr. 8	4-8
19	Stop Plate	304SS	1
20	Stop Pin	304SS	1

Size	ØB	ØC	ØD	E	ØG	L	H	S	ØK	ØM	T1	T2	n	ØN
2	4.75	3.62	1.97	9.72	6.00	7.00	4.45	0.374	2.76	16-18 UN	0.06	0.63	4	0.75
2-1/2	5.50	4.12	2.52	11.81	7.00	7.50	7.11	0.669	4.02	8-16 UN	0.06	0.69	4	0.75
3	6.00	5.00	2.99	11.81	7.50	8.00	7.47	0.669	4.02	8-16 UN	0.06	0.75	4	0.75
4	7.50	6.19	3.94	15.75	9.00	9.00	8.07	0.669	4.02	8-16 UN	0.06	0.94	8	0.87
6	9.50	8.50	5.91	39.37	11.00	15.50	11.14	0.906	4.92	2-13 UN	0.06	1.00	8	0.87

FNW™

4120 NE Columbia Blvd
Portland, OR 97211
Phone (503) 287-8383
Fax (503) 281-9677

TITLE/DESCRIPTION: Fig 660, 2PC, 150# FLANGED <RF>, STAINLESS STEEL xSTAINLESS STEEL, FULL PORT (Economy Version)

DATE: 8-3-2005 BY: UNITS: INCHES

SCALE: NONE APP'D: PAGE(S): 1

MODEL: 660

DWG NO: FNW660

NOTES:

FILE: 660_2-6.dwg WT: LOC: PORTLAND
PAGE SIZE: 8.5 x 11L REV: 0 RDATE:

THIS DRAWING CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF FNW VALVE AND IS SUBMITTED TO YOU FOR THE LIMITED PURPOSE OF PROVIDING YOU INFORMATION ON PRODUCTS AND SYSTEMS PURCHASED FROM FNW VALVE. BY RECEIVING THIS DOCUMENT, YOU AGREE NOT TO DISCLOSE SUCH INFORMATION TO OTHERS EXCEPT BY WRITTEN PERMISSION OF FNW VALVE.