

ONLY ONE COMPANY MAKES 10" & 15" INJECTION MOLDED GASKETED SEWER FITTINGS



Multi Fittings is the only manufacturer to offer gasketed 12" and 15" SDR 35 molded sewer fittings in a range of wyes, tees and elbows.

Ideal for wastewater and stormwater applications, as well as the conveyance of industrial wastes, our large diameter molded sewer fittings are designed to exceed all applicable standards and are built to withstand higher impact forces, higher loads and survive the roughest jobsite handling. The impact strength of our sewer fittings exceed the requirements of ASTM F1336 by at least 25%.

For over 50 years, Multi Fittings has been an industry leader in offering the most comprehensively engineered and tested fittings for plastic pipe in North America.

Multi Fittings produces the widest range of injection molded fittings for pressurized watermains and sewer forcemains, gravity flow sewers and drain, waste and vent applications.

TRENCH TOUGH PLUS™

SIZES

4" & 15"




MULTI FITTINGS

Telephone: 519 681-2140

Toll Free: 800 265-1815

Fax: 519 681-2156



Locked-in Gasket Design

Makes assembling the joints easy, requiring less brute force in the trench, while ensuring leak-proof reliability in the ground.

Advanced Material Formulation

Leading crush-resistance, yet our fittings can flex to accommodate the extreme loads that cause rigid fittings to fail.

Structural Reinforcements

Reinforced at key intersecting locations where it's needed for added strength without losing flexibility.

more information on back ►

FEATURES & BENEFITS

Easy to Install

Lightweight and easy to handle; with the patented Trench Tough Plus locked-in gasket design.

Joint Strength

Manufactured to allow for a high degree of joint deflection, reducing the risks caused by soil settlement or shifting.

Structural Strength

Leads the industry in crush-resistance and able to handle extreme loads underground.

Impact Strength

Designed to withstand the rigors of the job site, exceeding ASTM impact standards.



Telephone: 519 681-2140
Toll Free: 800 265-1815
Fax: 519 681-2156




MULTI FITTINGS


LAYING LENGTH

ISSUE DATE: OCT 30/17
SUPERCEDES: MAR 11/05

INCREASER COUPLING (GxG)



FABRICATED FITTING (F)



INJECTION MOLDED FITTING (M)

PS1 (SEWER)		SIZE H1xH2	PART NUMBER	N REF	PS (SEWER)
6.275	M =	6x4	043882	1.375	4.215
8.400	M =	8x4	043536	2.375	4.215
8.400	M =	8x6	043535	1.500	6.275
10.500	F @	10x8	043531	10.750	8.400
12.500	M =	12x4	143798	4.500	4.215
12.500	M =	12x6	143530	3.500	6.275
12.500	M =	12x8	143532	2.375	8.400
12.500	M =	12x10	143520	1.750	10.500
15.300	F @	15x10	043533	12.000	10.500
15.300	F @	15x12	043534	12.750	12.500
18.701	F @	18x15	043928	15.500	15.300
22.047	F @	21x15	043923	20.000	15.300
22.047	F @	21x18	043921	18.000	18.701
24.803	F @	24x18	043914	21.500	18.701
24.803	F @	24x21	043913	19.000	22.047

Note: = Refer to Page G4 for Hub Detail, Type A

@ Refer to Page G5 for Hub Detail, Fabricated