

Engineered Plastic (EP) Flow-through Multi-port Elbow

Submittal Information Revision B: June 7, 2010

Project Information

Job Name:

Location:	Part No. Ordered:					
Engineer:	Date Submitted:	Date Submitted:				
Contractor:	Submitted By:					
Manufacturer's Representative:	Approved By:					

Technical Data

Material: UDEL® Polysulfone GF120

Maximum Temperature (no


pressure): 320°F (160°C)

Maximum Working

Temperature/Pressure: 210°F at 150 psi (99°C at 10.3 bar)

Product Information and Application Use

Engineered Plastic (EP) Flow-through Multi-port Elbow features an integrated ¾" ProPEX® elbow with ½" ProPEX branch outlets. The elbow is designed for demanding, slab-on-grade, potable plumbing applications, and eliminates the need for multiple connections. The elbow is made of engineered plastic, a proven material in demanding hot-water applications.



✓ Description	Part Number	Α	В	С	D	E	Weight
EP Flow-through Multi-port Elbow, 3 outlets, 3/4" x 3/4"	Q2235577	6.03"	1.87"	1.25	0.75" ProPEX	0.75" ProPEX	0.10 lbs.
EP Flow-through Multi-port Elbow, 4 outlets, 3/4" x 3/4"	Q2245577	7.28"	1.87"	1.25	0.75" ProPEX	0.75" ProPEX	0.14 lbs.

Installation

Any product designed to mount 1" copper pipe (for the ¾" EP) or 1¼" copper pipe (for the 1" EP) is suitable for use as a mounting bracket. For more information, refer to the Uponor Professional Plumbing Installation Guide.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF 14- and 61-certified; ICC ESR 1099; Iapmo 3946; HUD MR 1269

Related Applications

Contact Information

PEX-a Plumbing Systems

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA

Phone: (800) 321-4739 Fax: (952) 891-2008 www.uponor-usa.com Uponor Ltd. 2000 Argentia Rd., Plaza 1, Ste. 200

Mississauga, ON L5N 1W1 CANADA Phone: (888) 994-7726 Fax: (800) 638-9517 www.uponor.ca

¹ProPEX[®] is a registered trademark of Uponor, Inc. ProPEX[™] is a trademark of Uponor Ltd.