



Brass Compression Fittings | #60C-4 [View Series Page](#)



\$0.37 /part

Local Manufacturer

Parker Hannifin Corporation

Fluid System Connectors Division

300 Parker Drive

Otsego, MI 49078 USA

UNITED STATES

Phone

+1 (269) 692-6555

Fax

+1 (269) 694-4614

Get your Parker account Today!

Create one account to manage everything you do with Parker, from your shopping preferences to your application access.

[Register now](#)

both forgings and extrusions compression fittings meet functional requirements of SAE J-512

➔ Share / Email

Technical Specifications

Shape:	Sleeve
Style:	Tube
Connection 3 Thread Size (inch):	na
O-Ring Material:	na
Connection 3 Tube O.D. (inch):	na
Connection 1 Thread Style:	na
Thread Type:	NPTF
Connection 1 Tube O.D. (inch):	1/4
Connection 2 Thread Size (inch):	na
Connection 1 Style:	Compression
Body Material:	Brass
Connection 2 Tube O.D. (inch):	na
Connection 2 Tube O.D. (mm):	na
Connection 2 Style:	na
Connection 1 Thread Size (metric):	na
Tube Material:	Copper, Aluminum, Thermoplastic
Nut Material:	Brass
Sleeve Material:	Brass, Acetal
Weight:	na
Media:	Water, air, inert and non-combustible gasses
Specifications Met:	SAE J-512, na
Maximum Operating Pressure:	20 bar, 300 psi
Maximum Operating Temperature:	250 °F, 121 °C
Minimum Operating Temperature:	-65 °F, -54 °C
Quantity per Box:	na
Application:	Compressors, Machine Tools, Engine, Pumps, Purification

⚠ WARNING: This product can expose you to chemicals including **Lead and Lead Compounds** which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE. This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise. The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors. To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems..... [Click here to view all product safety information.](#)

Based on your experience finding this product today, how likely are you to recommend Parker Hannifin to a friend or colleague?

Not at all likely Extremely likely

0	1	2	3	4	5	6	7	8	9	10
<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>

Item Information

Parker's compression fittings are economical and offered in both extrusions and forgings. These compression fittings require no flaring, soldering, tube preparation or special tools to operate. Compression fittings are especially useful in installations that may require occasional disassembly or partial removal for maintenance since the fitting can be broken and remade without affecting the integrity of the joint. Compression fittings are also used in situations where a heat source, in particular a soldering torch, is prohibited.

Use with copper, aluminum and the following Parker Parflex Division tubing:

- Polyethylene