

## ENGINEERING SUBMITTAL DATA

Metalfit manufactures Ductile Iron and Gray Cast Iron Flanged Fittings for both Waterworks and Industrial applications and conforms fully to the required industry standards. Flanged Fittings are manufactured in accordance with ANSI/AWWA C110/A21.10 and ANSI B16.1, Class 125. Metalfit 2" through 12" Flanged Fittings are also listed by Underwriters Laboratories for fire protection service. Additionally, **Metalfit hydrostatically tests every fitting** to ensure quality casting integrity. These tests are performed at 1.5 times the rated working pressure.

### Mechanical Properties

#### **Cast Iron to ASTM A48**

Minimum Tensile Strength 31,000 psi

#### **Ductile Iron to ASTM A 536**

Minimum Tensile Strength 70,000 psi

Yield Strength 50,000 psi

Elongation 5%

### Water Working Pressure

#### **Gray Cast Iron**

2" - 12" CI Fittings rated 250 psi

14" - 42" CI Fittings rated 150 psi

#### **Ductile Iron**

All DI Fittings Rated 250 psi

As noted in ANSI/AWWA C111/A21/11, ductile iron flanged joints in the 24" and smaller sizes may be rated to 350 psi with the use of "special" gaskets.

## COATINGS & LININGS

### Interior Linings

Flanged fittings are furnished cement lined and seal coated per ANSI/AWWA C104/A21.4. Fittings are also available unlined for air service or with other special linings for particular service conditions.

### Exterior Coatings


Flanged fittings are furnished standard with a red epoxy primer or tar coated at the customer's discretion. Special primer coatings are also available for particular service conditions.

**All standard coatings and linings are provided in full accordance with ANSI/NSF 61.**

## COMMITMENT TO QUALITY


Metalfit takes pride in producing the finest quality Flanged Fittings available in today's market. Our manufacturing standards and a strict adherence to the quality control procedures, developed over many years, make certain that we abide by our commitment to be the best.

## Flanged Joint Dimensions ANSI/AWWA C110/A21.10



Size	OD	BC	T	Hole Dia.	Bolt Size	No. Bolts
2	6.00	4.75	0.62	0.75	5/8 x 2-1/4	4
2-1/2	7.00	5.50	0.69	0.75	5/8 x 2-1/2	4
3	7.50	6.00	0.75	0.75	5/8 x 2-1/2	4
4	9.00	7.50	0.94	0.75	5/8 x 3	8
5	10.00	8.50	0.94	0.88	3/4 x 3	8
6	11.00	9.50	1.00	0.88	3/4 x 3-1/2	8
8	13.50	11.75	1.12	0.88	3/4 x 3-1/2	8
10	16.00	14.25	1.19	1.00	7/8 x 4	12
12	19.00	17.00	1.25	1.00	7/8 x 4	12
14	21.00	18.75	1.38	1.12	1 x 4-1/2	12
16	23.50	21.25	1.44	1.12	1 x 4-1/2	16
18	25.00	22.75	1.56	1.25	1-1/8 x 5	16
20	27.50	25.00	1.69	1.25	1-1/8 x 5	20
24	32.00	29.50	1.88	1.37	1-1/4 x 5-1/2	20
30	38.75	36.00	2.12	1.37	1-1/4 x 6-1/2	28
36	46.00	42.75	2.38	1.62	1-1/2 x 7	32
42	53.00	49.50	2.62	1.62	1-1/2 x 7-1/2	36
48	59.50	56.00	2.75	1.62	1-1/2 x 8	44


### BASE DIMENSIONS



Size	B.C.	Hole Dia.	No. Bolts
3	3.88	0.62	4
4	4.75	0.75	4
6	5.50	0.75	4
8	7.50	0.75	4
10	7.50	0.75	4
12	9.50	0.88	4
14	9.50	0.88	4
16	9.50	0.88	4
18	11.75	0.88	4
20	11.75	0.88	4
24	11.75	0.88	4
30	14.25	1.00	4
36	17.00	1.00	4
42	21.25	1.12	4
48	22.75	1.25	4

### INSTALLATION NOTE

Drilling Templates are furnished in multiples of four. Standard flanged reducers, with a different number of holes in each flange, will have only two centerlines which are common to the drilling templates of both flanges.



ANSI/AWWA C110/A21.10

Dimensions in inches.  
Weights in pounds.



## CERTIFICATE OF COMPLIANCE

Name: **U.S. Pipe Fabrication**

Date: **08/2017**

Job Name:

### PRODUCTS & MATERIAL

Metalfit manufactures Ductile Iron and Gray Iron AWWA C110 Flanged Fittings for both Waterworks and Industrial applications and conforms fully to all required industry standards. Metalfit also produces C 153 Mechanical Joint Fittings under the Griffin or GPP label in full compliance with those standards as well for both Griffin Pipe and Metalfit. Griffin C153 MJ Fittings have been produced by Metalfit since 2000. The production facility is located in Pesqueria, N.L. Mexico. We are a North American Free Trade Agreement producer.

We hereby certify that all materials furnished by Metalfit are manufactured and tested in accordance with the following standards, and meet or exceed the requirements and recommendations therein.

Cast Iron Flanged Fittings.....	ANSI B16.1, Class 250
Ductile Iron Flanged Fittings.....	ANSI / AWWA C110 / A21.10 ANSI B16.1, Class 125
Cast Iron Flanged Fittings.....	ANSI / AWWA C110 / A21.10 ANSI B16.1, Class 125
Ductile Iron Flanged Fittings.....	ASTM A 536 for Mechanical Properties
	Minimum Tensile Strength 70,000 psi
	Minimum Yield Strength 50,000 psi
	Minimum Elongation 5%
Cast Iron Flanged Fittings.....	ASTM A 48, minimum tensile 31,000 psi
Cement Mortar Lining.....	ANSI / AWWA C104 / A21.4
Protecto 401 Lining.....	In accordance with the "Licensed Applicator Agreement"
Standard Coatings and Linings.....	ANSI / NSF 61
Compact Mechanical Joint Fittings.....	ANSI / AWWA C153 / A21.53
Cast Iron Water Working Pressure.....	2" through 12" - 250 psi
	14" through 42" - 150 psi
Ductile Iron Water Working Pressure.....	2" through 42" - 250 psi
Ductile Iron Water Working Pressure.....	ANSI / AWWA C111 / A21 / 11, states that 2" through 24"
	may be rated to 350 psi with the use of "special" gaskets

Joe Gobeille  
Vice President

2023 Saint Louis Ave  
Bessemer, AL 35020

Byron Sanders  
Project Services Manager  
205-417-8416 Main  
864-616-6572 Cell  
bsanders@uspipe.com

# **STANDARD SPECIFICATION FOR LINING DUCTILE IRON PIPE FOR SEWER SERVICE**

## **I. Condition of Ductile Iron Prior to Surface Preparation**

All ductile pipe and fittings shall be delivered to the application facility without asphalt, cement lining, or any other lining on the interior surface. Because removal of old linings may not be possible, the intent of this specification is that the entire interior of the ductile iron pipe and fittings shall not have been lined with any substance prior to the application of the specified lining material and no coating shall have been applied to the first six inches of the exterior of the spigot ends.

## **II. Lining Material**

The Standard of Quality is PROTECTO 401 Ceramic Epoxy. The material shall be an amine cured novalac epoxy containing at least 20% by volume of ceramic quartz pigment. Any request for substitution must be accompanied by a successful history of lining pipe and fittings for sewer service, a test report verifying the following properties, and a certification of the test results.

- A. A permeability rating of 0.00 when tested according to Method A of ASTM E-96-66, Procedure A with a test duration of 30 days.
- B. The following test must be run on coupons from factory lined ductile iron pipe:
  - 1. ASTM B-117 Salt Spray (scribed panel) - Results to equal 0.0 undercutting after two years.
  - 2. ASTM G-95 Cathodic Disbondment 1.5 volts @ 77°F. Results to equal no more than 0.5 mm undercutting after 30 days.
  - 3. Immersion testing rated using ASTM D-714-87.
    - a. 20% Sulfuric acid—No effect after two years.
    - b. 140°F 25% Sodium Hydroxide—No effect after two years.
    - c. 160°F Distilled Water—No effect after two years.
    - d. 120°F Tap Water (scribed panel)—0.0 undercutting after two years with no effect.
- C. An abrasion resistance of no more than 3 mils (.075 mm) loss after one million cycles using European Standard EN 598: 1994 Section 7.8 Abrasion Resistance.

## **III. Application**

- A. Applicator  
The lining shall be applied by a certified firm with a successful history of applying linings to the interior of ductile iron pipe and fittings.
- B. Surface Preparation  
Prior to abrasive blasting, the entire area to receive the protective compound shall be inspected for oil, grease, etc. Any areas with oil, grease, or any substance that can be removed by solvent, shall be solvent cleaned to remove those substances. After the surface has been made free of grease, oil or other substances, all areas to receive the protective compounds shall be abrasive blasted using sand or grit abrasive media. The entire surface to be lined shall be struck with the blast media so that all rust, loose oxides, etc., are removed from the surface. Only slight stains and tightly adhering oxide may be left on the surface. Any area where rust reappears before lining must be reblasted.

- C. Lining  
After surface preparation and within 8 hours of surface preparation, the interior of the pipe shall receive 40 mils nominal dry film thickness of PROTECTO 401. No lining shall take place when the substrate or ambient temperature is below 40°F. The surface also must be dry and dust free. If flange pipe or fittings are included in the project, the lining shall not be used on the face of the flange.
- D. Coating of Bell Sockets and Spigot Ends  
Due to the tolerances involved, the gasket area and spigot end up to 6 inches back from the end of the spigot end must be coated with 6 mils nominal, 10 mils maximum using Protecto Joint Compound. The Joint Compound shall be applied by brush to ensure coverage. Care should be taken that the Joint Compound is smooth without excess buildup in the gasket seat or on the spigot ends. Coating of the gasket seat and spigot ends shall be done after the application of the lining.
- E. Number of Coats  
The number of coats of lining material applied shall be as recommended by the lining manufacturer. However, in no case shall this material be applied above the dry thickness per coat recommended by the lining manufacturer in printed literature. The maximum or minimum time between coats shall be that time recommended by the lining material manufacturer. **To prevent delamination between coats, no material shall be used for lining which is not indefinitely recoatable with itself without roughening of the surface.**
- F. Touch-Up and Repair  
Protecto Joint Compound shall be used for touch-up or repair in accordance with manufacturer's recommendations.

#### IV. Inspection and Certification

- A. Inspection
  - 1. All ductile iron pipe and fitting linings shall be checked for thickness using a magnetic film thickness gauge. The thickness testing shall be done using the method outlined in SSPC PA-2 Film Thickness Rating.
  - 2. The interior lining of all pipe barrels and fittings shall be tested for pinholes with a non-destructive 2,500 volt test. Any defects found shall be repaired prior to shipment.
  - 3. Each pipe joint and fitting shall be marked with the date of application of the lining system along with its numerical sequence of application on that date and records maintained by the applicator of his work.
- B. Certification  
The pipe or fitting manufacturer must supply a certificate attesting to the fact that the applicator met the requirements of this specification, and that the material used was as specified.

#### V. Handling

PROTECTO 401 lined pipe and fittings must be handled only from the outside of the pipe and fittings. No forks, chains, straps, hooks, etc. shall be placed inside the pipe and fittings for lifting, positioning, or laying. The pipe shall not be dropped or unloaded by rolling. Care should be taken not to let the pipe strike sharp objects while swinging or being off loaded. Ductile iron pipe should never be placed on grade by use of hydraulic pressure from an excavator bucket or by banging with heavy hammers.