



## LGR 3500i

Maximum drying - control humidity in spaces up to 17,000 cubic feet. Industry-leading performance in a highly durable and portable package. Automatically adjusts operation to maximize performance in high or low humidity conditions. The the digital control panel displays humidistat settings, real-time inlet and outlet temperatures and relative humidity and GPP.



## FEATURES

- Automatic humidistat control
- Displays inlet and outlet temperature and RH plus grain depression for easy monitoring
- Digital control panel with plain-English system messages, not codes.
- Rugged Dri-Eaz rotomolded housing is easy to maintain and won't mar furnishings.
- Automatic restart after outage when power is restored.

## SPECIFICATIONS

- **Water removal AHAM (80°F/60%RH):** 170 pts. | 80.4 L /day
- **Water removal Max. (90°F/90%RH):** 240 pts. | 113.6 L / day
- **Process Air:** 400 CFM | 679.7 CMH
- **Dimensions (W × H × D):** 24 × 40.5 × 23 in. | 61 × 103 × 58 cm
- **Use weight:** 158 lbs. | 71.2 kg
- **Amps:** 11.2A
- **Volts:** 115V
- **Frequency:** 60Hz
- **Air filter:** 4-PRO filter
- **Hose:** 40 ft. | 12.2 m
- **Power cord:** 25 ft. | 7.6 m detachable
- **Housing:** Rotomolded polyethylene
- **Safety:** ETL listed to CSA 22.2 no. 92
- **Xactimate:** WTRDHM>>>XXL

## SIZES ▪ OPTIONS

- **110133 (F411):** One unit